



Remote Speaker Microphone

RSM-EX01B..-D2NAM-1BBL...ST

- Extremely long operating times with high voice volume – Up to 78 hours
- Outstanding volume and sound performance – Up to 103 dB
- Good operability, even with gloves
- Lone worker ready (optional SOS button)
- Additional multi-functional buttons and a dedicated SOS button
- 2200 mAh Li-ion battery pack for a long operating time
- Linguistic feedback when changing individual modes
- Magnetic charging cable and optional charging cradle
- IoT Ready: "Custom Service Load" allows individual button settings for sending custom commands to servers and other IoT switches - e.g. to open a gate (only for Ex-Handy 10 Series)

RSM-Ex 01, Bluetooth, Division 1, version for Northern America



Connection

Division 2



Technical Data

Indicators/operating means

Key	PTT button operable with thick gloves Front-facing multi-function button Volume up / down Channel up / down On/Off switch Red Button
-----	---

Audio data

Sound level	up to 103 dB
-------------	--------------

Electrical specifications







Release date: 2023-06-27 Date of issue: 2023-06-27 Filename: 480984-100021_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Technical Data

Battery type	Li-Ion battery 3.7 V 2200 mAh
Operating duration	Stand-by time: approx. 74 h Actual use/operating time depending on use and set sound level (See table "Run times")
Communication	
Bluetooth	yes
NFC	yes
Ambient conditions	
Ambient temperature	-20 ... 60 °C (-4 ... 140 °F)
Mechanical specifications	
Degree of protection	IP 64 following EN/IEC 60079-0 (ATEX/ IECEx) IP 67 following EN/IEC 60529 (industrial standard)
International approvals	
SGS approval	
SGS certificate	SGSNA/20/SUW/00138X
SGS marking	CI I, II, III, Division 2, Groups A-G, T4 CI I Zn 2, AEx ic IIC T4 Gc CI II Zn 22, AEx ic IIIC T135°C Dc Ex ic IIC T4 Gc Ex ic IIIC T135°C Db Ta = -20 °C to +60 °C, IP 64
IECEX approval	
IECEX certificate	IECEX IBE 20.0004X
IECEX marking	Ex ia IIC T4 Ga Ex ia IIIC T135°C Db IP 64 Ex ia I Ma
Approved for	Northern America
General information	
Scope of delivery	RSM-Ex Charging cable Charger Safety instructions Documentation

Matching System Components








	Tab-Ex02-D02-WIFINAMDAN-DCS00..	Tab-Ex 02 D2 (DIV 2), latest available Android firmware release, WiFi, with camera, with microSD card, version for Northern America
	Tab-Ex02-D02-WWANNAMD-ANDCN00..	Tab-Ex 02 D2 (DIV 2), latest available Android firmware release, WWAN (LTE) incl. WiFi, with camera, version for Northern America
	Tab-Ex02-D02-WWANNAMD-ANDCS00..	Tab-Ex 02 D2 (DIV 2), latest available Android firmware release, WWAN (LTE) incl. WiFi, with camera, with microSD card, version for Northern America
	TAB-EX03-DZ2-WIFINAM-CN-000-..	Tab-Ex 03 DZ2 (Zone 2/22), latest available Android firmware release, WiFi, with camera, version for Northern America
	TAB-EX03-DZ2-WIFINAM-CS-000-..	Tab-Ex 03 DZ2 (Zone 2/22), latest available Android firmware release, WiFi, with camera, with microSD card, version for Northern America
	TAB-EX03-DZ2-WWANNAM-CN-000-..	Tab-Ex 03 DZ2 (Zone 2/22), latest available Android firmware release, WWAN (LTE) incl. WiFi, with camera, version for Northern America
	TAB-EX03-DZ2-WWANNAM-CS-000-..	Tab-Ex 03 DZ2 (Zone 2/22), latest available Android firmware release, WWAN (LTE) incl. WiFi, with camera, with microSD card, version for Northern America
	Smart-Ex02-ROW-DZ2AIC-ANDCEB..	Smart-Ex 02 DZ2 (DIV 2 and Zone 2/22), latest available Android firmware release, with camera, Camera Only Mode, global version

Release date: 2023-06-27 Date of issue: 2023-06-27 Filename: 480984-100021_eng.pdf









Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.comUSA: +1 330 486 0002
pa-info@us.pepperl-fuchs.comGermany: +49 621 776 2222
pa-info@de.pepperl-fuchs.comSingapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com
 **PEPPERL+FUCHS**

Matching System Components

	Smart-Ex02-ROW-DZ2AIC-ANDCES..	Smart-Ex 02 DZ21 (DIV 2 and Zone 2/22), latest available Android firmware release, with camera and eSENTINEL app, global version
	Smart-Ex02-ROW-DZ2AIC-ANDC00..	Smart-Ex 02 DZ2 (DIV 2 and Zone 2/22), latest available Android firmware release, with camera, global version
	Smart-Ex02-ROW-DZ2AIC-ANDN00..	Smart-Ex 02 DZ2 (DIV 2 and Zone 2/22), latest available Android firmware release, no camera, global version
	Ex-Handy10-ROW-DZ2AIC-ANDCEB..	Ex-Handy 10 DZ2 (DIV 2 and Zone 2/22), latest available Android firmware release, with camera, eBARCODE app preinstalled, global version
	Ex-Handy10-ROW-DZ2AIC-ANDC00..	Ex-Handy 10 DZ2 (DIV 2 and Zone 2/22), latest available Android firmware release, with camera, global version
	Ex-Handy10-ROW-DZ2AIC-ANDN00..	Ex-Handy 10 DZ2 (DIV 2 and Zone 2/22), latest available Android firmware release, no camera, global version
	RSM-HS 01-W	Lightweight duplex headset

Accessories

	EXT-C2LCOIL	Clip2Loop coil tether
	MINI QD LOOP	Mini QD loop
	RL ID01	Retractable lanyard for universal use
	CC S01-R	Car charger with USB-A socket for universal use
	DS RSM 01	Docking station for RSM
	TC S02 Travel Charger (EU/UK/US/AU)	Travel charger for universal use
	Charging Cable RSM	USB Charging Cable for RSM
	RSM-HS 01-W	Lightweight duplex headset

Operation

Run times**

Use time in % with typical user profiles speak/hear/standby	100% (Level 15 media; Level 8 phone call)	75% (Level 10 media; Level 4 phone call)	25% (Level 3 media; Level 2 phone call)
5 / 5 / 90	50 h	64 h	71 h
25 / 25 / 50	22 h	44 h	64 h
50 / 50 / 0	13 h	31 h	57 h
**determined runtimes on the Smart-Ex 02 based on RSM-Ex 01 BT software version 1.0.0			

Release date: 2023-06-27 Date of issue: 2023-06-27 Filename: 480984-100021_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".