



# Remote Speaker Microphone

## RSM-EX01B..-D1NAM-1BBLMOTST



- Extremely long operating times with high voice volume – Up to 78 hours
- Outstanding volume and sound performance – Up to 103 dB
- Good operability, even with gloves
- Lone worker ready (optional SOS button)
- Additional multi-functional buttons and a dedicated SOS button
- 2200 mAh Li-ion battery pack for a long operating time
- Linguistic feedback when changing individual modes
- Magnetic charging cable and optional charging cradle
- IoT Ready: "Custom Service Load" allows individual button settings for sending custom commands to servers and other IoT switches - e.g. to open a gate (only for Ex-Handy 10 Series)

RSM-Ex 01, Bluetooth, Motorola WAVE™, Division 1, version for Northern America



### Connection

Division 1



### Technical Data

#### Indicators/operating means

Key	PTT button operable with thick gloves Front-facing multi-function button Volume up / down Channel up / down On/Off switch Red Button
-----	---

#### Audio data

Sound level	up to 103 dB
-------------	--------------

#### Electrical specifications

Release date: 2023-06-27 Date of issue: 2023-06-27 Filename: 480984-100034\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com








Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com



## Technical Data

Battery type	Li-Ion battery 3.7 V 2200 mAh
Operating duration	Stand-by time: approx. 74 h Actual use/operating time depending on use and set sound level (See table "Run times")
<b>Communication</b>	
Bluetooth	yes
NFC	yes
Connections	Motorola WAVE™ For all Android™ and Apple iOS devices (including the latest Tab-Ex® Series) connected via Bluetooth® Supported and tested PTT applications: Motorola WAVE™
<b>Ambient conditions</b>	
Ambient temperature	-20 ... 60 °C (-4 ... 140 °F)
<b>Mechanical specifications</b>	
Degree of protection	IP 64 following EN/IEC 60079-0 (ATEX/ IECEx) IP 67 following EN/IEC 60529 (industrial standard)
<b>International approvals</b>	
SGS approval	
SGS certificate	SGSNA/20/SUW/00138X
SGS marking	CI I, II, III, Div.1, GRPS A-G, T4, T135°C CI I, Zn 1, AEx ib IIC T4 Gb IP64 CI II, Zn 21, AEx ib IIIC T135°C Db IP64 CI I, Zn 1, Ex ib IIC T4 Gb IP64 CI II, Zn 21, Ex ib IIIC T135°C Db IP64
IECEX approval	
IECEX certificate	IECEX IBE 20.0004X
IECEX marking	Ex ia IIC T4 Ga Ex ia IIIC T135°C Db IP 64 Ex ia I Ma
Approved for	Northern America
<b>General information</b>	
Scope of delivery	RSM-Ex Charging cable Charger Safety instructions Documentation

## Matching System Components





	<b>Tab-Ex02-DZ1-WIFINAM-ANDCS00..</b>	Tab-Ex 02 DZ1 (DIV 1 and Zone 1/21), latest available Android firmware release, WiFi, with camera, with microSD card, version for Northern America
	<b>Tab-Ex02-DZ1-WIFINAM-ANDCS00HM</b>	Tab-Ex 02 DZ1 (DIV 1 and Zone 1/21), latest available Android firmware release, WiFi, with camera, with microSD card, including HART modem, version for Northern America
	<b>Tab-Ex02-DZ1-WWANNAM-ANDCS00NC</b>	Tab-Ex 02 DZ1 (DIV 1 and Zone 1/21), latest available Android firmware release, WWAN (LTE) incl. WiFi, with camera, with microSD card, no charger, version for Northern America
	<b>Smart-Ex02-ROW-DZ1AIC-ANDCES..</b>	Smart-Ex 02 DZ1 (DIV 1 and Zone 1/21), latest available Android firmware release, with camera and eSENTINEL app, global version
	<b>Smart-Ex02-ROW-DZ1AIC-ANDC00..</b>	Smart-Ex 02 DZ1 (DIV 1 and Zone 1/21), latest available Android firmware release, with camera, global version
	<b>Smart-Ex02-ROW-DZ1AIC-ANDN00..</b>	Smart-Ex 02 DZ1 (DIV 1 and Zone 1/21), latest available Android firmware release, no camera, global version
	<b>Ex-Handy10-ROW-DZ1AIC-ANDCEB..</b>	Ex-Handy 10 DZ1 (DIV 1 and Zone 1/21), latest available Android firmware release, with camera, eBARCODE app preinstalled, global version

Release date: 2023-06-27 Date of issue: 2023-06-27 Filename: 480984-100034\_eng.pdf









Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.comUSA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.comGermany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.comSingapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com
 **PEPPERL+FUCHS**

## Matching System Components

	<b>Ex-Handy10-ROW-DZ1AIC-ANDCES..</b>	Ex-Handy 10 DZ1 (DIV 1 and Zone 1/21), latest available Android firmware release, with camera, eSENTINEL app, global version
	<b>Ex-Handy10-ROW-DZ1AIC-ANDC00..</b>	Ex-Handy 10 DZ1 (DIV 1 and Zone 1/21), latest available Android firmware release, with camera, global version
	<b>Ex-Handy10-ROW-DZ1AIC-ANDN00..</b>	Ex-Handy 10 DZ1 (DIV 1 and Zone 1/21), latest available Android firmware release, no camera, global version
	<b>RSM-HS 01-W</b>	Lightweight duplex headset

## Accessories

	<b>EXT-C2LCOIL</b>	Clip2Loop coil tether
	<b>MINI QD LOOP</b>	Mini QD loop
	<b>RL ID01</b>	Retractable lanyard for universal use
	<b>CC S01-R</b>	Car charger with USB-A socket for universal use
	<b>DS RSM 01</b>	Docking station for RSM
	<b>TC S02 Travel Charger (EU/UK/US/AU)</b>	Travel charger for universal use
	<b>Charging Cable RSM</b>	USB Charging Cable for RSM
	<b>RSM-HS 01-W</b>	Lightweight duplex headset

**Operation**

Run times\*\*

Use time in % with typical user profiles speak/hear/standby	100% (Level 15 media; Level 8 phone call)	75% (Level 10 media; Level 4 phone call)	25% (Level 3 media; Level 2 phone call)
5 / 5 / 90	50 h	64 h	71 h
25 / 25 / 50	22 h	44 h	64 h
50 / 50 / 0	13 h	31 h	57 h

\*\*determined runtimes on the Smart-Ex 02 based on RSM-Ex 01 BT software version 1.0.0

Release date: 2023-06-27 Date of issue: 2023-06-27 Filename: 480984-100034\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".