



# Smartphone



## Smart-Ex02-ROW-DZ2AIC-ANDN00..

- Replaceable SIM
- Global certificates - a common hardware platform
- Wireless connections such as WWAN, 4G LTE, WLAN and Bluetooth®
- Android™ Enterprise Recommended verified device
- GPS
- NFC technology for wireless applications
- Service contract
- Special buttons for lone worker protection (LWP) applications
- Programmable hardware buttons
- Android™ 11 operating system

Smart-Ex 02 DZ2 (DIV 2 and Zone 2/22), latest available Android firmware release, no camera, global version



### Technical Data

Hardware	
Processor	Qualcomm Snapdragon 450
RAM	3 GByte
Optional data memory	Micro SD flash card up to 128 GByte
Internal data memory	32 GByte
Speaker	Forward facing main speaker with Gore® cone
Microphone	Dual-mic solution with three selectable background noise suppression options
Indicators/operating means	
Display	Extreme shock and scratch resistant Gorilla® Glass with glove touch and wet mode
Touchscreen technology	Capacitive multitouch
Screen diagonal	12.7 cm
Resolution	720 x 1280 pixels
Key	PTT / Alarm / Power / Multifunction / Volume / Hardware buttons for Android features
Electrical specifications	
Battery type	Li-Ion battery 16.28 WH 3.7 V 4400 mAh
Operating duration	LTE standby time: up to 350 h
Communication	
Mobile standard	
2G	GSM: 850 MHz, 900 MHz, 1800 MHz, 1900 MHz
3G	UMTS: 850 MHz, 900 MHz, 1700 MHz, 1900 MHz, 2100 MHz
4G	LTE FDD: B1, B2, B3, B4, B5, B7, B8, B11, B12, B13, B20, B21, B25, B26, B28, B66, B71 LTE TDD: B38, B39, B40, B41
WLAN	802.11 a/b/g/n/ac/e/k/r/h (2,4 GHz + 5 GHz)
Bluetooth	Bluetooth® 4.2
GPS sensor	GPS, A-GPS, Glonass, Beidou, Galileo
NFC	yes
SIM card	Dual Nano-SIM
Software	
Operating system	Android™ 11 Android™ Enterprise Recommended verified device
SMS/MMS	yes
Ambient conditions	







Release date: 2022-06-01 Date of issue: 2022-06-01 Filename: 480986-100009\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".













## Technical Data

Ambient temperature	-20 ... 60 °C (-4 ... 140 °F)
<b>Mechanical specifications</b>	
Degree of protection	IP68 , MIL-STD-810G
Connection	7-pins water-proof magnetic USB 2.0 port 3.5 mm jack connection with special ecom mounting solution
Mass	approx. 380 g
<b>Dimensions</b>	
W x H x D	82 mm x 163 mm x 22 mm
<b>Data for application in connection with hazardous areas</b>	
ATEX approval	
ATEX certificate	EPS 19 ATEX 1 069 X
ATEX marking	Ⓜ II 3G Ex ic op is IIC T4 Gc IP64 Ⓜ II 3D Ex ic op is IIIC T120°C Dc Ta = -20 °C to +60 °C
<b>International approvals</b>	
SGS approval	
SGS certificate	Class I, II, III, Division 2 Group A-G T4 IP 64 Ex ic IIC T4 Gc Ex ic IIIC T120°C Dc CI I Zn 2, AEx ic IIC T4 Gc Zn 22, AEx ic IIIC T120°C Dc Ta = -20 °C to +60 °C, IP 64
IECEX approval	
IECEX certificate	IECEX EPS 19.0032X
IECEX marking	Ex ic op is IIC T4 Gc IP64 Ex ic op is IIIC T120°C Dc Ta = -20 °C to +60 °C
Approved for	Albania, Australia, Austria, Azerbaijan, Belgium, Bosnia-Herzegovina, Brunei, Bulgaria, Canada, Ceuta, Croatia, Czech Republic, Denmark, Egypt, Estonia, Finland, France, Germany, Greece, Hungary, Iceland, India, Iraq, Ireland, Israel, Italy, Kuwait, Latvia, Liechtenstein, Lithuania, Luxembourg, Macedonia, Malaysia, Malta, Mexico, Montenegro, Myanmar, Netherlands, New Zealand, Norway, Oman, Peru, Philippines, Poland, Portugal, Romania, Saudi Arabia, Serbia, Singapore, Slovak Republic, Slovenia, Spain, Sweden, Switzerland, Thailand, Turkey, United Arab Emirates, United Kingdom, Uzbekistan, Vietnam, USA
<b>General information</b>	
Note	Android is a trademark of Google LLC.
Scope of delivery	Smart-Ex® 02 Li-Ion battery Charger USB cable Screwdriver Documentation

## Accessories

	<b>RL ID01</b>	Retractable lanyard
	<b>SUCTION CUP HOLDER</b>	Suction cup holder for Smart-Ex 02 and Ex-Handy 10
	<b>LH S02</b>	Leather holster
	<b>Ex-BP S02</b>	Battery pack
	<b>TC S02 Travel Charger (EU/UK/US/AU)</b>	Travel charger
	<b>TORX T8 SCREWDRIVER</b>	Torx screwdriver for Smart-Ex® 02 and Ex-Handy 10

## Accessories

	<b>EXT-C2LCOIL</b>	Clip2Loop coil tether
	<b>MINI QD LOOP</b>	Mini QD loop
	<b>LC S02</b>	Leather case for Smart-Ex® 02
	<b>DS S02</b>	Docking station
	<b>CC S01-R</b>	Car charger
	<b>BC-Ex</b>	Belt clip with QuickFix
	<b>DC EX-BP S02</b>	Battery pack charger for Ex-BP S02 & BP S02
	<b>ST 01</b>	Stylus pen
	<b>CR-EX S02</b>	Cradle for Smart-Ex® 02
	<b>Tether ST 01 Stylus</b>	Stylus tether
	<b>PC S02</b>	USB Charging Cable for Smart-Ex 02, Ex-Handy 10 and Pocket Unit PU-Ex V01
	<b>SC-Ex</b>	Spring clip with 4QuickFix