



Tablet computer

Tab-Ex® 03 DZ2

TAB-EX03-DZ2-WIFINAM-CS-000-..



- NFC technology for wireless applications
- Comprehensive security thanks to Samsung KNOX
- Suitable for use with gloves
- Google ARCore
- Samsung DeX Mode
- MIL-STD-810H
- 64 GB internal memory
- Micro SD slot (up to 1 TB)
- Micro SD slot, 512 GB
- 13 MP rear camera + 5 MP front camera
- Verizon, AT&, T-Mobile

Tab-Ex 03 DZ2 (DIV 2 and Zone 2/22), latest available Android firmware release, WiFi, with camera, with microSD card, version for Northern America



Technical Data

Hardware	
Processor	Octa-core, 4 x 2.7 GHz + 4 x 1.7 GHz Exynos 9810
RAM	4 GB
Camera	
Front camera	5 MP
Main camera	13 MP Autofocus
Video recording resolution	UHD 4K (3840 x 2160 Pixel) @ 30 fps
Internal data memory	64 GByte Free available memory 48.6 GByte
Optional data memory	microSD (up to 1024 GB) 512 GB installed
Sensors	Acceleration sensor, gyroscope, proximity sensor, geomagnetic sensor, Hall sensor, RGB light sensor
Speaker	yes
Indicators/operating means	
Display	Can be operated while wearing gloves
Touchscreen technology	Capacitive multitouch
Type	TFT, LCD
Screen diagonal	20.31 cm
Aspect ratio	16:10
Resolution	1920 x 1200 (WUXGA)
Brightness	480 cd/m ² (nit)
Colors	16 Mio.
Electrical specifications	
Battery type	Li-Ion 18.87 WH, 3.8 V 5050 mAh (typical) 4900 mAh (rated)
Operating duration	up to 11 h
Communication	
WLAN	802.11 a/b/g/n/AC/ax 2.4 G+5 GHz, HE80, MIMO, 1024 QAM
Bluetooth	Bluetooth® 5.0
GPS sensor	GPS, Glonass, Beidou, Galileo

Release date: 2024-04-29 Date of issue: 2024-04-29 Filename: 480988-100030_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com



Technical Data

USB	USB 3.1 Gen. 1
Connections	Wi-Fi Direct, NFC, ANT+
Software	
Operating system	Android™ 13
Safety	Samsung KNOX 3.x
Ambient conditions	
Ambient temperature	-20 ... 55 °C (-4 ... 131 °F)
Mechanical specifications	
Degree of protection	IP64 according to EN/IEC 60079-0 (ATEX/IECEX) IP68* according to EN/IEC 60529 (industrial standard) and MIL-STD-810H
Mass	610 g
Dimensions	
W x H x D	126.8 mm x 213.8 mm x 9.9 mm
Data for application in connection with hazardous areas	
ATEX approval	
Certificate of conformity	EPS 21 ATEX 1 093 X
ATEX marking	Ⓜ II 3G Ex ic IIC T5 Gc IP64 Ⓜ II 3D Ex ic IIIC T85°C Dc
International approvals	
SGS approval	
SGS certificate	SGSNA/21/SUW00045X
Approved for	Class I, Division 2 Groups A, B, C, D T5 Class II, Division 2 Groups F, G T100°C Class III Class I, Zone 2 Group IIC T5 Zone 22 Group IIIB T100°C
IECEX approval	
IECEX certificate	IECEX EPS 21.0033X
IECEX marking	Ex ic IIC T5 Gc IP64 Ex ic IIIC T85°C Dc
Approved for	Northern America
Further approvals	MIL-STD-810H
General information	
Scope of delivery	Tab-Ex® 03 Battery Ex-protective cover S Pen USB cable Charger Documentation Micro SD flash card

Accessories

Accessories for this product can be found on the internet at www.pepperl-fuchs.com.