



Tablet computer

Tab-Ex® 03 DZ1

TAB-EX03-DZ1-WWANNAM-CS-000-..



- NFC technology for wireless applications
- Comprehensive security thanks to Samsung KNOX
- Suitable for use with gloves
- Google ARCore
- Samsung DeX Mode
- MIL-STD-810H
- 64 GB internal memory
- Replaceable SIM
- Wireless connections such as WWAN, 4G LTE, WLAN and Bluetooth®
- Micro SD slot, 512 GB
- 13 MP rear camera + 5 MP front camera
- Verizon, AT&, T-Mobile

Tab-Ex 03 DZ1 (DIV 1 and Zone 1/21), latest available Android firmware release, WWAN (LTE) incl. WiFi, with camera, with microSD card, version for Northern America



Technical Data

Hardware	
Processor	Octa-core, 4 x 2.7 GHz + 4 x 1.7 GHz Exynos 9810
RAM	4 GB
Camera	
Front camera	5 MP
Main camera	13 MP Autofocus
Video recording resolution	UHD 4K (3840 x 2160 Pixel) @ 30 fps
Internal data memory	64 GByte Free available memory 48.6 GByte
Optional data memory	microSD (up to 1024 GB) 512 GB installed
Sensors	Acceleration sensor, ambient light sensor, gyroscope, geomagnetic sensor, Hall sensor,
Speaker	yes
Indicators/operating means	
Display	Can be operated while wearing gloves
Touchscreen technology	Capacitive multitouch
Type	TFT, LCD
Screen diagonal	20.31 cm
Aspect ratio	16:10
Resolution	1920 x 1200 (WUXGA)
Brightness	480 cd/m ² (nit)
Colors	16 Mio.
Electrical specifications	
Battery type	Li-Ion 18.87 WH, 3.8 V 5050 mAh (typical) 4900 mAh (rated)
Operating duration	up to 11 h
Communication	

Release date: 2024-04-05 Date of issue: 2024-04-05 Filename: 480989-100024_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com



Technical Data

Mobile standard		
3G		UMTS: B1, B2, B4, B5, B8
4G		LTE FDD: B2, B3, B4, B5, B7, B8, B12, B13, B14, B20, B25, B26, B29, B66, B71 LTE TDD: B41
WLAN		802.11 a/b/g/n/AC/ax 2.4 G+5 GHz, HE80, MIMO, 1024 QAM
Bluetooth		Bluetooth® 5.0
GPS sensor		GPS, Glonass, Beidou, Galileo
USB		USB 3.1 Gen. 1
Connections		Wi-Fi Direct, NFC, ANT+
SIM card		1x Nano SIM (4FF)
Software		
Operating system		Android™ 13
Safety		Samsung KNOX 3.x
SMS/MMS		yes
Ambient conditions		
Ambient temperature		-20 ... 50 °C (-4 ... 122 °F)
Mechanical specifications		
Degree of protection		IP64 according to EN/IEC 60079-0 (ATEX/IECEX)
Mass		1100 g
Dimensions		
W x H x D		161.5 mm x 262.75 mm x 25.75 mm
International approvals		
IECEX approval		
IECEX certificate		IECEX EPS 22.0014X
IECEX marking		Ex db ia IIC T6 Gb Ex ia tb IIIC T80°C Db
ETL approval		
Approved for		5027822
Approved for		Class I, Division 1, Groups A, B, C, D, T6 Class I, Zone 1, AEx db ia IIC T6 Gb Ex db ia IIC T6 Gb
Approved for		Northern America
Further approvals		MIL-STD-810H
General information		
Scope of delivery		Tab-Ex® 03 S Pen USB cable Charger Documentation Micro SD flash card

Accessories

Accessories for this product can be found on the internet at www.pepperl-fuchs.com.