



Tablet computer

Tab-Ex® 05 DZ1

TAB-EX05-DZ1-WWANAIN-CN1000-..

- Android™ 15 operating system
- Portable rugged tablet with brilliant 8" display
- Comprehensive security thanks to Samsung KNOX
- Suitable for use with gloves
- Google ARCore
- Fast data transfer via 5G connectivity
- Robust and protected against falls according to IP68 and MIL-STD-810H
- Function button for quick access

WWAN (LTE) incl. Wi-Fi, with camera, for Europe and Northern America



Technical Data

Hardware

Processor	Exynos 1380 (S5E8835) Octa-Core 4 x 2.4 GHz + 4 x 2.0 GHz 64 Bit, 5 nm
RAM	6 GB LPDDR4X
Camera	
Front camera	5 MP 1/5.0" sensor, F2.2 aperture
Main camera	13 MP 1/3.0" sensor, F1.9 aperture, autofocus, 8x digital zoom
Video recording resolution	UHD 4K (3840 x 2160) @ 30 fps
Internal data memory	128 GB UFS
Optional data memory	microSD (up to 1 TB)
Sensors	Accelerometer, Gyro Sensor, Geomagnetic Sensor, Hall Sensor, RGB Light Sensor
Speaker	yes

Indicators/operating means

Display	
Refresh rate	Standard (60 Hz) / Adaptive (up to 120 Hz)
Touch screen technology	Capacitive
Panel type	TFT
Screen size	20.31 cm / 8 inch
Aspect ratio	16:10
Screen resolution	1920 x 1200 (WUXGA)
Pixel density	283 ppi
Brightness	max. 600 cd/m ² (nits)
Colors	16 Mio.
Screen protection	Corning® Gorilla® Glass 3
Special Features	Can be operated while wearing gloves Dark Mode, Adaptive Brightness, Eye Comfort, Screen Saver, Screen Zoom, Multi-Touch
Key	Function button, Active button

Electrical specifications

Battery type	Li-ion 3.8 V 5050 mAh 18.87 Wh (typically)
Operating duration	up to 14 h

Interface

Release date: 2026-04-07 Date of issue: 2026-04-07 Filename: 480996-100013_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Technical Data

I/O ports	USB 2.0 (Type-C)
Communication	
Mobile standard	
4G	LTE FDD: B1 (2100), B2 (1900), B3 (1800), B4 (AWS), B5 (850), B7 (2600), B8 (900), B12 (700), B13 (700), B17 (700), B20 (800), B26 (850), B28 (700), B32 (1500), B66 (AWS 3), B68 (700) LTE TDD: B38 (2600), B40 (2300), B41 (2500) 4x4 MIMO: B1 (2100), B3 (1800), B4 (AWS), B7 (2600), B66 (AWS 3), B38 (2600), B41 (2500)
5G	Sub6 FDD: N1 (2100), N3 (1800), N5 (850), N7 (2600), N8 (900), N20 (800), N26 (850), N28 (700), N66 (AWS 3), N71 (600) Sub6 TDD: N38 (2600), N40 (2300), N41 (2500), N77 (3700), N78 (3500) 4x4 MIMO: N1 (2100), N3 (1800), N7 (2600), N66 (AWS 3), N38 (2600), N40 (2300), N41 (2500), N77 (3700), N78 (3500)
WLAN	WLAN 802.11 a/b/g (2.4 GHz), WiFi 4, 5, 6 (2.4 GHz + 5 GHz), HE80, MIMO, 1024 QAM, WiFi Direct, Mobile Hotspot, Hotspot 2.0, Auto Hotspot
Bluetooth	Bluetooth® 5.3
GPS sensor	GPS, Glonass, Beidou, Galileo
NFC	yes
Connections	Wireless DeX
SIM card	Nano (4FF) / eSIM (optional)
Software	
Operating system	Android™ 15 Android™ Enterprise Recommended verified device Google ARCore ready
Cybersecurity	
IT security	
Biometrics	Facial recognition
Updates	Security updates until 2032 Operating system upgrades up to Android™ 22
Mobile device protection	Samsung KNOX 3.10
Ambient conditions	
Ambient temperature	-20 ... 55 °C (-4 ... 131 °F)
Mechanical specifications	
Degree of protection	IP68 according to EN/IEC 60529 MIL-STD-810H
Mass	approx. 1122 g
Dimensions	
Height	26 mm
Width	162 mm
Length	263 mm
Data for application in connection with hazardous areas	
ATEX approval	
ATEX certificate	EPS 24 ATEX 1 288 X
ATEX marking	Ⓜ II 2G Ex db ia IIC T6 Gb Ⓜ II 2D Ex tb ia IIIC T80°C Db
International approvals	
SGS approval	
SGS certificate	SGSNA/25/CA/00003X
SGS marking	Class I Division 1, Group A, B, C, D, T6 Class II Division 1, Group E, F, G T80C Class III T80C Ex db ia IIC T6 Gb Class I, Zone 1, AEx db ia IIC T6 Gb Zone 21, Group IIIC T80C Ambient Temperature: -20°C = Ta = +55°C
IECEx approval	
IECEx certificate	IECEx EPS 24.0082X

Release date: 2026-04-07 Date of issue: 2026-04-07 Filename: 480996-100013_eng.pdf

Technical Data

IECEX marking	Ex db ia IIC T6 Gb Ex tb ia IIC T80°C Db
Approved for	Europe, USA , Iraq, Chile, Guyana, Panama, Morocco, El Salvador, Israel, Egypt, Trinidad and Tobago
General information	
Scope of delivery	Tab-Ex® 05 Torx T8 S Pen USB cable Charger Documentation Optional: Micro SD flash card Viator Bluetooth HART Interface

Accessories

Accessories for this product can be found on the internet at www.pepperl-fuchs.com.