



VisuNet RM Shell Emerson DRDC License Key

VISUNET-RM-SHELL4-DRDC

- Allows you to directly connect from a VisuNet Remote Monitor to a virtualized Emerson DeltaV system

Function

Pepperl+Fuchs VisuNet Remote Monitors (VisuNet RM) are industrial grade Thin Client solutions that provide a simplified, modern User Interface to the Operators. The firmware of a VisuNet RM, called VisuNet RM Shell, enables the users to easily access the applications that run on a process control systems via Ethernet.

With the RM Shell 4.0 DRDC License key, the EMERSON DRDC client can be enabled in the RM Shell 4.0:

The EMERSON DeltaV® Remote Desktop Connection (DRDC) client allows you directly connecting to a virtualized Emerson DeltaV system from a VisuNet Remote Monitor. No addition thin clients are required in the safe area. Furthermore, all features of a VisuNet Remote Monitor (like auto-connect, connection loss detection, backup connection, etc.) can be used for a DRDC connection, which gives you the maximum reliability in your process automation application.

Technical Data

Software	
Operating system	based on Microsoft Windows Embedded Standard 7
Languages	English
Licensing	
Available licenses	1x license key to enable "DeltaV Remote Desktop Connection (DRDC) Client" features of one VisuNet Remote Monitor with pre-installed RM Shell 4.x
Installation	Licenses can only be enabled in the RM Shell 4.x by user role "Adminstrator".
Associated products	VisuNet Remote Monitors with pre-installed RM Shell 4.x

Release date: 2023-12-11 Date of issue: 2023-12-11 Filename: 547751_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

License Bundles

Product	Number of Licenses	Part Number
VISUNET-RM-SHELL4-DRDC-5	5	548008
VISUNET-RM-SHELL4-DRDC-10	10	548009
VISUNET-RM-SHELL4-DRDC-30	30	548010

Release date: 2023-12-11 Date of issue: 2023-12-11 Filename: 547751_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com