

VisuNet RM Shell Control Center License Key

VISUNET-RM-SHELL4-CC



- Enables easy, centralized management of a Remote Monitor via the VisuNet Control Center

Function

Pepperl+Fuchs VisuNet Remote Monitors (VisuNet RM) are industrial grade Thin Client solutions that provide a simplified, modern user interface to the operators. The firmware of a VisuNet RM, called VisuNet RM Shell, enables the users to easily access the applications that run on a process control systems via Ethernet.

With the CC License key, the „VisuNet Control Center interface“ feature can be enabled in the RM Shell 4.1 (or newer).

This interface enables a Remote Monitor to be centralized managed via the VisuNet Control Center. This includes functions like download/upload of profiles, changing device settings and allows shadowing a session from the Control Center.

Technical Data

Software

Operating system	based on Microsoft Windows Embedded Standard 7
Languages	English
Licensing	
Available licenses	1x license key to enable "Control Center interface" feature of one VisuNet Remote Monitor with pre-installed RM Shell 4.1 (or newer)
Installation	Licenses can only be enabled in the RM Shell 4.1 (or newer) by user role "Administrator".
Associated products	VisuNet Remote Monitors with pre-installed RM Shell 4.1 VisuNet Control Center

License Bundles

Product	Number of Licenses	Part Number
VISUNET-RM-SHELL4-CC-5	5	548030
VISUNET-RM-SHELL4-CC-10	10	548031
VISUNET-RM-SHELL4-CC-30	30	548032

Release date: 2023-12-11 Date of issue: 2023-12-11 Filename: 548024_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com