Features

 Allows you to directly connect from a VisuNet Remote Monitor to a virtualized Emerson DeltaV system

Application

Pepperl+Fuchs VisuNet Remote Monitors (VisuNet RMs) are industrial-grade thin client solutions that give operators a simplified, modern user interface. The firmware of a VisuNet RM, called VisuNet RM Shell, enables users to easily access applications that run on process control systems via Ethernet. With the RM Shell 5 DRDC license key, the EMERSON DRDC client can be enabled in the RM Shell 5:

The EMERSON DeltaV® Remote Desktop Connection (DRDC) client allows direct connection to a virtualized Emerson DeltaV system from a VisuNet RM. No additional thin clients are required in the safe area. Further, all features of a VisuNet RM (such as auto-connect, connection loss detection, backup connection, etc.) can be used for a DRDC connection, which gives you maximum reliability in your process automation application.

DRDC License



Software		
Operating system	based on Microsoft Windows 10 IoT Enterprise LTSB	
Languages	English	
Licensing		
Available licenses	1x license key to enable "DeltaV Remote Desktop Connection (DRDC) Client" features of one VisuNet Remote Monitor with pre-installed RM Shell 5.x	
Installation	Licenses can only be enabled in the RM Shell 5.x by user role "Adminstrator".	
Associated products	VisuNet Remote Monitors with pre-installed RM Shell 5.x	

License Bundles

Product	Number of Licenses	Part Number
VISUNET-RM-SHELL5-DRDC-5	5	548295
VISUNET-RM-SHELL5-DRDC-10	10	548296
VISUNET-RM-SHELL5-DRDC-30	30	548297
VISUNET-RM-SHELL5-DRDC-50	50	548298