


Bulk Spiral Cable

SPK 5x0,25mm² BL900/200/300

- Resistant to microbes and hydrolysis
- UV resistant
- Halogen-free

Spiral Cable, PUR/PUR, 5-core black

Dimensions



Technical Data


General specifications		
Customization		sheath stripped , with wire end ferrule
Electrical specifications		
Operating voltage	U_B	max. 250 V AC/DC
Conformity		
Product standard		on the basis of DIN VDE 0812
Ambient conditions		
Ambient temperature		-25 ... 80 °C (-13 ... 176 °F)
Pollution degree		3
Mechanical specifications		
Cable		according to IEC/EN 60228 (DIN VDE 0295) class 6
Sheath diameter		5.8 mm
Sheath color		black (similar to RAL 9005)
Number of cores		5
Core cross section		0.25 mm²
Cores color		Core 1: white Core 2: brown Core 3: green Core 4: yellow Core 5: black
Core construction		65 x 0.07 mm Ø
Length	L	1.4 m extension length max. 3.6 m BL: 900 mm A1: 200 mm A2: 34 mm A3: 6 mm B1: 300 mm B2: 34 mm B3: 6 mm
Cable code		Li F 11Y 11Y 5 x 0,25
Mass		300 g
Material		
Halogen-free		yes

Release date: 2024-07-05 Date of issue: 2024-07-05 Filename: 64314745_eng.pdf

Technical Data

Cable		
Sheathing		TMPU
Cores		bare copper (Cu)
Core insulation		TMPU
UV resistance		yes
Oil resistance		yes
Microbial resistance		yes
Hydrolysis resistance		yes

Connection Assignment



Release date: 2024-07-05 Date of issue: 2024-07-05 Filename: 64314745_eng.pdf