


Bulk Spiral Cable

SPK 3x0,5mm² BL750/200/200

- Resistant to microbes and hydrolysis
- UV resistant
- Halogen-free

Spiral Cable, PUR/PUR, 3-core black

Dimensions



Technical Data


General specifications		
Customization		sheath stripped , with wire end ferrule
Electrical specifications		
Operating voltage	U_B	max. 250 V AC/DC
Conformity		
Product standard		on the basis of DIN VDE 0812
Ambient conditions		
Ambient temperature		-25 ... 80 °C (-13 ... 176 °F)
Pollution degree		3
Mechanical specifications		
Cable		according to IEC/EN 60228 (DIN VDE 0295) class 6
Sheath diameter		5 mm
Sheath color		black (similar to RAL 9005)
Number of cores		3
Core cross section		0.5 mm²
Cores color		Core 1: white Core 2: brown Core 3: green
Core construction		64 x 0.1 mm Ø
Length	L	1.15 m extension length max. 3 m BL: 750 mm A1: 200 mm A2: 54 mm A3: 6 mm B1: 200 mm B2: 54 mm B3: 6 mm
Cable code		Li F 12Y 11Y 3 x 0,5
Mass		240 g
Material		
Halogen-free		yes
Cable		

Release date: 2024-07-05 Date of issue: 2024-07-05 Filename: 64314769_eng.pdf

Technical Data

Sheathing	TMPU
Cores	bare copper (Cu)
Core insulation	TPE-E
UV resistance	yes
Oil resistance	yes
Microbial resistance	yes
Hydrolysis resistance	yes

Connection Assignment



Release date: 2024-07-05 Date of issue: 2024-07-05 Filename: 64314769_eng.pdf