

Headset

Ex-TRA 30 LH NH Zone 2 ATEX

- Certified according to latest ATEX standards
- For use in ATEX Zone 2
- Available in three different hearing protection headset versions

Intrinsically Safe Headset for ATEX Zone 2, Neckband and Helmet (Light Headset)

Technical Data

General specifications		
Description		Light headphones - neck strap and helmet
Hardware		
Speaker		32 Ohm at 1 kHz (+/- 15%)
Microphone		Max. 2200 Ohm bei 1 kHz
Ambient conditions		
Operating temperature		-20 ... 50 °C (-4 ... 122 °F)
Storage temperature		-20 ... 50 °C (-4 ... 122 °F)
Mechanical specifications		
Degree of protection		IP54
Connector		3.5 mm plug with screw
Cable		
Length	L	38 cm, extendable to 130 cm
Mass		60 g
Data for application in connection with hazardous areas		
ATEX approval		
ATEX certificate		PF20CERT5579X
ATEX marking		Ⓔx II 3G Ex ic IIA T4 Gc Ta = -20 °C to +60 °C
General information		
Scope of delivery		Headset Documentation

Release date: 2021-07-08 Date of issue: 2021-07-08 Filename: 70111125_eng.pdf