

Headset

Ex-TRA 30 EPH N Zone 2 ATEX

- Certified according to latest ATEX standards
- For use in ATEX Zone 2
- Available in three different hearing protection headset versions

Intrinsically Safe Headset for ATEX Zone 2, Neckband

Technical Data

General specifications		
Description		Behind-The-Neck
Hardware		
Speaker		30 Ohm at 1 kHz (+/- 15%)
Microphone		Max. 4400 Ohm bei 1 kHz
Ambient conditions		
Operating temperature		-20 ... 50 °C (-4 ... 122 °F)
Storage temperature		-20 ... 50 °C (-4 ... 122 °F)
Mechanical specifications		
Connector		3.5 mm plug with screw
Cable		coiled
Length	L	50 cm - 130 m
Mass		380 g
Data for application in connection with hazardous areas		
ATEX approval		
ATEX certificate		PF19CERT5391X
ATEX marking		Ⓔx II 3G Ex ic IIA T4 Gc Ta = -20 °C to +60 °C
General information		
Scope of delivery		Headset Documentation

Release date: 2021-06-30 Date of issue: 2021-06-30 Filename: 70111127_eng.pdf