


SFP: 100BASE-LX Fast Ethernet Single-mode Fiber

SFP-S-30KM-F-N




- Industry standard small form pluggable (SFP) package
- SFP Multi-Source Agreement compliant
- Hot pluggable
- Class 1 laser product complies with EN 60825-1
- Single power supply 3.3V
- TTL signal detect indicator
- Duplex LC connector
- Temperature range: 0 to 70° C

Single-mode 30KM 100BASE-LX Fast Ethernet Fiber SFP



Dimensions



Technical Data

Ethernet Interface		
Standards		
IEEE802.3u 100BASE-LX		yes
Interface 1		
Interface type		100BASE-LX Fast Ethernet Fiber
Physical		SFP, Hot pluggable
Transfer rate		155 Mbps
Fiber optics functionality		
Wave length		1310 nm

Release date: 2024-08-21 Date of issue: 2024-08-21 Filename: 70116429_eng.pdf

Technical Data

Cable type	9/125µm Single-mode
Cable length	max. 30 km
Connector type	1 Duplex LC
Transmit power (optical)	-15 ... -8 dBm
Receive sensitivity	-34 ... 0 dBm
Link budget	19 dB
Directive conformity	
Electromagnetic compatibility	
Directive 2014/30/EU	EN55024, IEC 61000-4-2, IEC 61000-4-3, IEC 61000-4-4, IEC 61000-4-6, IEC 61000-4-8
Standard conformity	
Emitted interference	CISPR 22 , FCC Part 15 Subpart B Class A , EN61000-6-4, IEC61000-6-4
Noise immunity	EN 55024
Standards	SFP Multi-Source (MSA) compliant Class 1 laser product complies with EN 60825-1
Ambient conditions	
Ambient temperature	0 ... 70 °C (32 ... 158 °F)
Storage temperature	-40 ... 85 °C (-40 ... 185 °F)
Relative humidity	max. 95 %
Mechanical specifications	
Mass	17 g
Dimensions	
Height	8.5 mm
Width	13.4 mm
Length	56.5 mm

Release date: 2024-08-21 Date of issue: 2024-08-21 Filename: 70116429_eng.pdf