

Explosion-protected LED flashlight

3AA ELED CPO ET12P



- Zone 0/20
- High / Low Power Modus
- Dust and waterproof (up to 3 m)
- Corrosion-resistant
- Pressure equalisation system

Explosion-protected LED flashlight



Technical Data

General specifications

Bulb	2 W high performance LED
Luminous flux	110 lumens (high power) 22 lumens (low power)

Electrical specifications

Battery type	3x LR06 / AA (type-tested)
Operating duration	6-8 hrs (high power) 6-30 hrs (low power)

Ambient conditions

Ambient temperature	-20 ... 40 °C (-4 ... 104 °F)
Storage temperature	-40 ... 50 °C (-40 ... 122 °F)

Mechanical specifications

Degree of protection	IP67
Mass	approx. 150 g (with batteries)
Dimensions	
W x H x D	approx. 134 mm x 41 mm x 35 mm

Release date: 2022-01-20 Date of issue: 2022-01-20 Filename: 70117761_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".