

Docking station ICZ-HH50-CHARGER



Docking station for IC-HH51 and IC-HH52



Technical Data

Indicators/operating means

LED red/green	Power: green/off Charge: green/red Connect: green/off
---------------	---

Input

Input voltage	100 V AC ... 240 V AC 47 ... 63 Hz
Input current	max. 1 A

Output

Output current	2.4 A
Output voltage	15 V DC

Directive conformity

Electromagnetic compatibility	
Directive 2014/30/EU	EN 301489-1 EN 55032 EN 55035
RoHS	
Directive 2011/65/EU (RoHS)	IEC/EN 63000

Standard conformity

Degree of protection	EN 60529
----------------------	----------

Approvals and certificates

CE conformity	CE
---------------	----

Ambient conditions

Ambient temperature	0 ... 40 °C (32 ... 104 °F)
Storage temperature	-20 ... 60 °C (-4 ... 140 °F)

Mechanical specifications

Degree of protection	IP20
Connection	Ethernet: RJ-45 USB 2.0 (Type A)
Material	
Housing	aluminum / ABS
Mass	approx. 557 g
Dimensions	
Height	82 mm
Width	200 mm
Length	138 mm

Release date: 2024-04-02 Date of issue: 2024-04-02 Filename: 70119702_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

 PEPPERL+FUCHS