



Countersunk profile rail PGV-PR-GM-CLOSE100

Sturdy construction

Countersunk rail for mounting in a floor groove

Dimensions





Technical Data

General specifications	
Length	150 mm
Width	60 mm
Ambient conditions	
Operating temperature	-40 80 °C (-40 176 °F)
Installation temperature	10 40 °C (50 104 °F)
Mechanical specifications	
Material thickness	4 mm
Material	AIMg4.5Mn0.7
Surface	ELOX-E0EV1-15

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Technical Data	
Mass	84 g

Mounting

Countersunk profile rails are embedded into a pre-milled groove in the floor. These are glued or screwed into the floor groove depending on the application. The milled floor groove is then grouted with suitable filler material. The groove for the countersunk profile rails must be protected against penetration of glue or filler material during installation. Once the filler material has dried out, the corresponding metal code bar is inserted into the countersunk profile rails via the self-adhesive rear side. If necessary, metal code bars that have been glued in can be replaced by levering them out.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

