

Countersunk profile plate
PGV-PP-GM-TAGM4x4



- Sturdy construction

Countersunk plate for mounting in a floor groove

Dimensions



Technical Data

General specifications		
Length		100 mm
Width		100 mm
Ambient conditions		
Operating temperature		-40 ... 80 °C (-40 ... 176 °F)
Installation temperature		10 ... 40 °C (50 ... 104 °F)
Mechanical specifications		
Material thickness		4 mm
Material		AlMg4.5Mn0.7
Surface		ELOX-E0EV1-15

Release date: 2022-07-01 Date of issue: 2022-07-04 Filename: 70132459_eng.pdf

Technical Data

Mass		90 g

Countersunk profile plates are embedded into a pre-milled groove in the floor. These are glued or screwed into the floor groove depending on the application. The milled floor groove is then grouted with suitable filler material. The groove for the countersunk profile plates must be protected against penetration of glue or filler material during installation. Once the filler material has dried out, the corresponding metal control code bar is inserted into the countersunk profile rails via the self-adhesive rear side. If necessary, metal control code bars that have been glued in can be replaced by levering them out.

Accessories

	**PGV-PR-GM-CONT100**	Countersunk rail for realization of continuous tracks

Release date: 2022-07-01 Date of issue: 2022-07-04 Filename: 70132459_eng.pdf