

Mounting set


MHV-BT-F10-M12

- Simple mounting
- All-in-one stainless steel solution
- Conforming to standards
- Adjustable in height

Adjustable assembly set for sizes F10 manual operated valves according to EN ISO5211 with threaded hole M12

Release date: 2023-09-19 Date of issue: 2023-09-25 Filename: 70134295_eng.pdf

Dimensions



Technical Data

General specifications	
Suitable sensors and	Double sensors, -F25 series with actuator BT32... Double sensors, -F25K series with actuator BT32... Double sensors, -F31 series with actuator BT65... Double sensors, -F31K series with actuator BT65... Double sensors, -F31K2 series with actuator BT65...
Standard conformity	
Standards	DIN EN ISO 5211 / DIN 3337
Mechanical specifications	

Release date: 2023-09-19 Date of issue: 2023-09-25 Filename: 70134295_eng.pdf

Technical Data

Material	stainless steel 1.4301 / AISI 304 for plates and sheet metal bending parts
Mass	419 g
General information	
Note	For the mounting set, an adapter plate and depending on this, and further accessories must be ordered.
Scope of delivery	Three threaded pins with hexagon socket, various lengths 2 counter nuts 1 drive screw

Matching System Components

	**MHV-BT-F25/F31**	Adapter plate for double sensors -F25/-F31 series
	**MHV-BT-F31K/F31K2**	Adapter plate for double sensors F31K/-F31K2 series

Release date: 2023-09-19 Date of issue: 2023-09-25 Filename: 70134295_eng.pdf