

# Flashlight

## 2AAA eLED PEN I - ETB LED Penlight



- Zones 1, 21
- Dust and waterproof (up to 1 m)
- Rubberised switch

Explosion-protected LED flashlight (ATEX Zone 1/21)



### Technical Data

#### General specifications

Bulb	0.5 W high performance LED
Luminous intensity	1000 Lux (1 m distance)
Luminous flux	approx. 35 lumens

#### Electrical specifications

Battery type	2x LR03 / AAA (type-tested)
Operating duration	approx. 3 h (continuous operation)

#### Ambient conditions

Ambient temperature	-20 ... 40 °C (-4 ... 104 °F)
Storage temperature	-40 ... 60 °C (-40 ... 140 °F)

#### Mechanical specifications

Degree of protection	IP67
Mass	approx. 102 g (with batteries)
Dimensions	
W x H x D	approx. 135 mm x 25 mm x 22 mm

#### Data for application in connection with hazardous areas

EU-type examination certificate	SEV 11 ATEX 0174 X
Marking	Ⓜ II 2G Ex ib IIB T4 Gb Ⓜ II 2D Ex ib IIIC T60°C Db