



## Base station for IDM-Z2-\* (Zone 2/22) IDM-Z2-x64-B-J2-BT-N0

- Base/charging station for IDM-Z2-x61-M-\* Bluetooth® handheld readers
- Certified for ATEX and IECEx Zone 2/22
- Bluetooth interface

Base station for IDM-Z2-\* (Zone 2/22)



### Function

IDM-Z2-x64-B-\* Bluetooth® base/charging stations are used with IDM-Z2-x64-M-\* handheld readers. Several connection cables are available as accessories for connectivity to Pepperl+Fuchs VisuNet HMI components. Additional models are available for non-hazardous areas.

### Technical Data

#### General specifications

Radio distance (in open air) max. 100 m

#### Electrical specifications

Operating voltage  $U_B$  6.5 V DC

Current consumption 1.1 A

#### Interface

Interface type Bluetooth V4.0 EDR , Class 1  
Electrical interfaces: RS-232 , USB

Transmitter frequency 2.4 ... 2.4835 GHz (ISM band)

#### Directive conformity

##### Electromagnetic compatibility

Directive 2014/30/EU EN 61000-6-2:2005 + AC:2005 , EN 61000-6-4:2007 + A1:2011

##### Explosion protection

Directive 2014/34/EU EN 60079-0:2018  
EN 60079-11:2012

##### Radio and telecommunication terminal equipment

Directive 2014/53/EU EN 300328 V2.1.1:2016 , EN 301489-1 V2.2.0:2017 , EN 301489-17 V3.2.0:2017

##### RoHS

Directive 2011/65/EU (RoHS) EN 50581:2012

#### Conformity

Supplementary standard conformity EN 60950-1:2006+A1:2010+A2:2013+A11:2009+A12:2011

#### Ambient conditions

Operating temperature -20 ... 50 °C (-4 ... 122 °F)

Storage temperature -40 ... 70 °C (-40 ... 158 °F)

Relative humidity 95 % non-condensing

#### Mechanical specifications

Degree of protection IP40

#### Data for application in connection with hazardous areas

EU-type examination certificate IBExU19ATEXB016X  
IECEx IBE 19.0026X

Release date: 2023-07-04 Date of issue: 2023-07-04 Filename: 70158522\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com






Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

## Technical Data

Marking	Zone 2/22 II 3G Ex ic IIC T4 Gc II 3D Ex ic IIIC T135°C Dc
<b>General information</b>	
Supplementary information	Observe the certificates, declarations of conformity, instruction manuals, and manuals where applicable. For information see <a href="http://www.pepperl-fuchs.com">www.pepperl-fuchs.com</a> .

## Accessories

	<b>HOLDER-BRACKET-XX00-IDMx61-B-N</b>	Stainless steel bracket to mount IDM-Zx-x6x-B-Jx-BT-N0 base station to AG-XX00 housing
	<b>HOLDER-BRACKET-3200-IDMx61-B-N</b>	Stainless steel bracket to mount IDM-Zx-x6x-B-Jx-BT-N0 base station to AG-3200 housing
	<b>HOLDER-BRACKET-AG1-IDMx61-B-N0</b>	Stainless steel bracket to mount IDM-Zx-x6x-B-Jx-BT-N0 base station to AG1 housing
	<b>CBL-IDMx61-B-Jx-S-S07-N0</b>	Accessory cable for IDM-Zx-x6x-M-* Bluetooth® handheld readers
	<b>CBL-IDMx61-B-Jx-U-S07-N0</b>	Accessory cable for IDM-Zx-x6x-M-* Bluetooth® handheld readers