



## Control Center License Key VISUNET-RM-SHELL6-CC

- Enables easy, centralized management of a Remote Monitor via the VisuNet Control Center

### VisuNet Control Center License Key for RM Shell 6

## Function

Pepperl+Fuchs VisuNet Remote Monitors (VisuNet RMs) are industrial- grade thin client solutions that give users a simplified, modern user interface. The firmware of a VisuNet RM, called VisuNet RM Shell, enables users to easily access applications that run on process control systems via Ethernet.

With the CC license key, the "VisuNet Control Center interface" feature can be enabled in the RM Shell 6.x (or newer). This interface enables an RM to be centrally managed via the VisuNet Control Center. This allows functions such as downloading/uploading profiles, changing device settings, and session shadowing.

## Technical Data

Software	
Operating system	Compatible with Microsoft Windows 7 and newer and .Net Framework 4.7.2 required
Languages	English
Licensing	
Available licenses	1x license key to enable "Control Center interface" feature of one VisuNet Remote Monitor with pre-installed RM Shell 6.x (or newer)
Installation	Licenses can only be enabled in the RM Shell 6.x (or newer) by user role "Administrator".
Associated products	VisuNet Remote Monitors with pre-installed RM Shell 6.x VisuNet Control Center

## Product Versions

### Shell 6 CC

Part No.	Model Number
XSP2-037-01R	VISUNET-RM-SHELL6-CC-DLK
70162159	VISUNET-RM-SHELL6-CC
70162160	VISUNET-RM-SHELL6-CC-5
70162161	VISUNET-RM-SHELL6-CC-10
70162162	VISUNET-RM-SHELL6-CC-30
70162164	VISUNET-RM-SHELL6-CC-50

Release date: 2023-05-11 Date of issue: 2023-05-11 Filename: 70162159\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**