



# DRDC License Key

## VISUNET-RM-SHELL6-DRDC

- Allows you to directly connect from a VisuNet Remote Monitor to a virtualized Emerson DeltaV system

### DRDC License Key for RM Shell 6

## Function

Pepperl+Fuchs VisuNet Remote Monitors (VisuNet RMs) are industrialgrade thin client solutions that give operators a simplified, modern user interface. The firmware of a VisuNet RM, called VisuNet RM Shell, enables users to easily access applications that run on process control systems via Ethernet.

With the RM Shell 6 DRDC license key, the EMERSON DRDC client can be enabled in the RM Shell 6:

The EMERSON DeltaV® Remote Desktop Connection (DRDC) client allows direct connection to a virtualized Emerson DeltaV system from a VisuNet RM. No additional thin clients are required in the safe area. Further, all features of a VisuNet RM (such as autoconnect, connection loss detection, backup connection, etc.) can be used for a DRDC connection, which gives you maximum reliability in your process automation application.

## Technical Data

Software	
Operating system	Based on Microsoft® Windows 10 IoT Enterprise LTSC 2021
Languages	English
Licensing	
Available licenses	1x license key to enable "DeltaV Remote Desktop Connection (DRDC) Client" features of one VisuNet Remote Monitor with pre-installed RM Shell 6.x
Installation	Licenses can only be enabled in the RM Shell 6.x (or newer) by user role "Administrator".
Associated products	VisuNet Remote Monitors with pre-installed RM Shell 6.x

Release date: 2023-05-11 Date of issue: 2023-05-11 Filename: 70162169\_eng.pdf

Product Versions

Shell 6 DRDC

Part No.	Model Number
XSP2-037-02R	VISUNET-RM-SHELL6-DRDC-DLK
70162169	VISUNET-RM-SHELL6-DRDC
70162170	VISUNET-RM-SHELL6-DRDC-5
70162171	VISUNET-RM-SHELL6-DRDC-10
70162172	VISUNET-RM-SHELL6-DRDC-30
70162173	VISUNET-RM-SHELL6-DRDC-50

Release date: 2023-05-11 Date of issue: 2023-05-11 Filename: 70162169\_eng.pdf