

PRO License Key

VISUNET-RM-SHELL6-PRO

- Restricted Web browser (Internet Explorer-based): Allows the secure direct access of HTML-based MES and SCADA systems
- Restricted Web browser (Chrome-Engine-based): HTML5 compatible web browser that enables the secure access of websites and web-applications.
- Desktop Sharing: Clone a Remote Monitor to work with one host system from several Remote Monitors simultaneously
- Raritan KVM Profile: Client allows to directly connect to Raritan Dominion KX II-101 V2 KVM-Switch

PRO License Key for RM Shell 6


Function

Pepperl+Fuchs VisuNet Remote Monitors (VisuNet RMs) are industrialgrade thin client solutions that give operators a simplified, modern user interface. The firmware of a VisuNet RM, called VisuNet RM Shell, enables users to easily access applications that run on process control systems via Ethernet. With the RM Shell 6 pro license key, additional features can be enabled in RM Shell 6. Refer to the feature table to see which features are unlocked.

Technical Data

| Software | |
|---------------------|---|
| Operating system | Based on Microsoft® Windows 10 IoT Enterprise LTSC 2021 |
| Languages | English |
| Licensing | |
| Available licenses | 1x license key to enable "Pro" features of one VisuNet Remote Monitor with pre-installed RM Shell 6.x |
| Installation | Licenses can only be enabled in the RM Shell 6.x (or newer) by user role "Administrator". |
| Associated products | VisuNet Remote Monitors with pre-installed RM Shell 6.x |

Accessories

| | | |
|---|-----------------|-------------------------------------|
|  | DKX4-101 | Raritan Dominion KVM-over-IP Switch |
|---|-----------------|-------------------------------------|

Release date: 2023-05-11 Date of issue: 2023-05-11 Filename: 70162174_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Features unlocked with PRO License (#548289)

| Features | Description |
|--|---|
| Restricted web browser, based on Internet Explorer | Fast HTML browser that uses Internet Explorer for rendering websites. Operators can be restricted to specified websites. |
| Restricted web browser, based on Chrome engine | Fast HTML5 browser that uses the Google Chrome rendering engine. Operators can be restricted to specified websites. |
| Desktop sharing | This feature allows users to clone a Remote Monitor and display its desktop on other VisuNet Remote Monitors (requires RM Shell 4.0.3 or later) |
| Raritan KVM profile | Client allows direct connection to Raritan Dominion KX II-101 V2 KVM-Switch |

Product Versions

Shell 6 PRO

| Part No. | Model Number |
|--------------|---------------------------|
| XSP2-037-03R | VISUNET-RM-SHELL6-PRO-DLK |
| 70162174 | VISUNET-RM-SHELL6-PRO |
| 70162175 | VISUNET-RM-SHELL6-PRO-5 |
| 70162176 | VISUNET-RM-SHELL6-PRO-10 |
| 70162177 | VISUNET-RM-SHELL6-PRO-30 |
| 70162178 | VISUNET-RM-SHELL6-PRO-50 |

Release date: 2023-05-11 Date of issue: 2023-05-11 Filename: 70162174_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".