

Mounting set


MHV-BT-F10


- Simple mounting
- All-in-one stainless steel solution
- Conforming to standards
- Adjustable in height


Adjustable assembly set for sizes F10 manual operated valves according to EN ISO5211 (without drive screw)


Release date: 2024-01-31 Date of issue: 2024-01-31 Filename: 70173262_eng.pdf

Dimensions









Technical Data

General specifications	
Suitable sensors and	Dual sensors, -F25 series with actuator BT32... Dual sensors, -F25K series with actuator BT32... Dual sensors, -F31 series with actuator BT65... Dual sensors, -F31K series with actuator BT65... Dual sensors, -F31K2 series with actuator BT65...
Standard conformity	
Standards	DIN EN ISO 5211 / DIN 3337
Mechanical specifications	

Release date: 2024-01-31 Date of issue: 2024-01-31 Filename: 70173262_eng.pdf

Technical Data

Material	stainless steel 1.4301 / AISI 304 for plates and sheet metal bending parts
Mass	316 g
Dimensions	
Width	64 mm
Length	312 mm
General information	
Note	For the mounting set, an adapter plate and depending on this, and further accessories must be ordered.

Release date: 2024-01-31 Date of issue: 2024-01-31 Filename: 70173262_eng.pdf