
Bulk Raw Cable
CBL-PVC-BU-04x075-100M



Cable, PVC/PVC, 4-core blue

Dimensions



Technical Data


Electrical specifications		
Operating voltage	U_B	max. 300 V AC/DC
Conformity		
Flammability		IEC 60332-2-1
Ambient conditions		
Ambient temperature		
Cable, fixed installation		-15 ... 105 °C (5 ... 221 °F)
Cable, flexing		-15 ... 105 °C (5 ... 221 °F)
Pollution degree		3
Mechanical specifications		
Cable		according to IEC/EN 60228 (DIN VDE 0295) class 5
Sheath diameter		6.8 mm ± 0.2 mm
Bending radius		> 6 x cable diameter, movable installation &t; 3 x cable diameter, fixed installation
Sheath color		blue (similar to RAL 5015)
Number of cores		4
Core cross section		0.75 mm²
Cores color		Core 1: brown Core 2: white Core 3: blue Core 4: black
Core construction		24 x 0.2 mm Ø
Length	L	100 m
Cable code		Li YY 4 x 0,75
Mass		5070 g
Material		

Release date: 2025-02-14 Date of issue: 2025-02-14 Filename: 70178421_eng.pdf

Technical Data

Cable		
Sheathing		PVC
Cores		bare copper (Cu)
Core insulation		PVC
Flammability		flame-resistant

Connection Assignment



Release date: 2025-02-14 Date of issue: 2025-02-14 Filename: 70178421_eng.pdf