



Self-Service POS Tablet and Kiosk Terminal

Tab-IND®

TAB-IND15WINAA1A3XX.1

- Flexible installation with countertop or floor stands using standardized VESA 75/100 mounts or custom furniture/wall integration
- Combines the power of a kiosk with the flexibility of a tablet in a compact design
- Contactless Payment and Checkout Directly on the Screen
- Front facing NFC antenna
- Developed in-house

Self-Service POS Tablet and Kiosk Terminal with integrated NFC payment module, 15.6 inches, Android

Technical Data

Hardware		
Processor		Qualcomm® QCS6490 Octa-Core 2.1 GHz
RAM		8 GByte
Camera		
Front camera		5 MP as optional accessory
Internal data memory		128 GByte UFS
Speaker		integrated
Microphone		integrated
Indicators/operating means		
Display		
Touch screen technology		Multi-touch
Panel type		TFT, LCD
Screen size		15.6 inch (39.62 cm)
Aspect ratio		9:16
Screen resolution		1080 x 1920 px
Brightness		350 cd/m²
Special Features		Cover glass with anti-glare treatment
Interface		
I/O ports		1x USB-C 2.0 on the rear 3 x USB-C 2.0 on each side for connecting accessories 1 x USB-C 3.2 on the right-hand side for connecting accessories or for service purposes 1x USB-A in host mode on the rear RJ-45 LAN with PoE function DC input (barrel connector) 24 V at 3 A
Communication		
WLAN		WLAN IEEE 802.11 ax
Bluetooth		Bluetooth® 5.2
NFC		Front-facing NFC antenna (top right, illuminated symbol) Optimized for payment processing Supports transport cards (Felica, MiFare), EMVCo L1 approved SoftPOS applications from various partners available
Software		
Operating system		Android™ 15 with GMS
Ambient conditions		
Operating temperature		-10 ... 50 °C (14 ... 122 °F)

Release date: 2026-04-16 Date of issue: 2026-04-16 Filename: 70206536_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**

Technical Data

Storage temperature	-20 ... 60 °C (-4 ... 140 °F)	
Relative humidity		10 % ... 90 %
Mechanical specifications		
Installation		VESA mounting pattern: 70 x 70 mm 100 x 100 mm
Mass	approx. 3 kg (incl. power supply)	
Dimensions		
Height	348.5 mm	
Width		238.8 mm
Depth	31.3 mm	
International approvals		
Approved for	EU, UK, USA	
General information		
Scope of delivery	Tab-IND® Power supply 24 V / 3 A / 72 W	

Accessories

Accessories for this product can be found on the internet at www.pepperl-fuchs.com.