


Dimensions






10.2

M18 x 1




Electrical connection



Pinout



Indicators/operating means



1	Signal display yellow		
2	Operating display green		
3	Sensitivity adjustment		



CE

Model Number

ML17-54/115b/127

Retroreflective sensor with fixed cable and M12 connector, 4-pin

Features

- ٠ Compact series in universal housing for standard applications
- Miniature design ٠
- Front mounting with M18-threads or ٠ side mounting holes
- 360° high visibility LEDs •
- Time-saving mounting with quick • clamp system
- Version with polarized filters detect ٠ shiny objects

Pepperl+Fuchs Group www.pepperl-fuchs.com

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com


Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Technical data		
General specifications		
Effective detection range		0 3.5 m
Reflector distance		50 3500 mm
Threshold detection range		5 m
Reference target		FE-RR1 reflector
Light source		LED
Light type		modulated visible red light , 626 nm
Polarization filter		yes
Ambient light limit		≤ 10000 Lux
Indicators/operating means		
Operation indicator		LED green
Function indicator		LED yellow, lights up with receiver lit
Control elements		sensitivity adjustment
Electrical specifications		
Operating voltage	UB	10 30 V DC , class 2
Ripple		max. 10 %
No-load supply current	I ₀	< 25 mA
Operating current		100 mA max per output
Time delay before availability	t _v	≤ 200 ms
Output		
Switching type		light/dark on
Signal output		2 NPN short-circuit protected, protected against reverse polarity, open collector
Switching voltage		max. 30 V DC
Switching current		max. 100 mA
Voltage drop	Ud	≤ 2 V DC
Switching frequency	f	500 Hz
Response time		≤ 1 ms
Ambient conditions		
Ambient temperature		-20 55 °C (-4 131 °F)
Storage temperature		-40 75 °C (-40 167 °F)
Mechanical specifications		
Degree of protection		IP67
Connection		fixed cable 150 mm with M12 x 1 male connector, 4 pin
Material		
Housing		ABS
Optical face		Acrylic
Mass		approx. 23 g
Compliance with standards and ves	directi	
Standard conformity		
Product standard		EN 60947-5-2:2007 IEC 60947-5-2:2007
Approvals and certificates		
UL approval		cULus
CCC approval		CCC approval / marking not required for products rated \leq 36 V
		eee approvant maning not required for producio rated 200 V

Curves/Diagrams



Accessories

OMH-ML17-EZ Mounting bracket


OMH-ML17 Mounting bracket

OMH-ML17-1 Mounting bracket

Other suitable accessories can be found at www.pepperl-fuchs.com



www.pepperl-fuchs.com



Pepperl+Fuchs Group www.pepperl-fuchs.com

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

