


# Dimensions

**Technical data** 



## **Model Number**

### V1D-M12H-V45-Y917140

Panel mount, adapter RJ45 socket to M12 socket D-coded

### **Features**

- · Front/screw mounting
- Suitable for 2-, 3- and 4-wire technology
- Panel mount connection adapter
- M12 D-coded to RJ45 (Shielded to coupling)

General specifications		
Number of pins	4	
Connection 1	socket	
Construction type 1	straight	
Threading 1	M12	
Connection 2	Male connector	
Construction type 2	straight	
Threading 2	RJ-45	
Electrical specifications		
Operating voltage L	max 42 V DC	
Operating current	max 1.5 A	
Ambient conditions		
Ambient temperature	-40 80 °C (-40 17	76 °F)
Mechanical specifications		
Degree of protection	IP67	
Material		
Contacts	Gold plated copper al	loy
Housing	PBT	
Connector	nickel-plated brass	
Slotted nut	nickel-plated brass	
General information		
Note	Category 5 : RJ-45 co	nnector
Compliance with standards and di tives		
Standard conformity		
Standards	CAT5 (IEC 11801:200 IEC 61076-2-101:200	02) , CAT5e (TIA 568B:2001) 8

## **Electrical connection**

