

Model Number

1/2"NPT-V1D-GN1M-PVC-V45-G

Ethernet bus cable, M12 D-coded to RJ45, PVC cable 4-pin, CAT5e, shielded

Features

- Front/screw mounting
- Suitable for 2-, 3- and 4-wire technology
- Ethernet receptacle
- 4-pin female D-coded M12 to cabled male RJ45 connector
- 1/2"NPT-14 mounting

Dimensions

Technical data

General specifications

Number of pins	4
Connection 1	socket
Construction type 1	straight
Threading 1	M12
Connection 2	Male connector
Construction type 2	straight
Threading 2	RJ-45

Electrical specifications

Operating voltage	U_B	max ... 60 V DC
Operating current	I_B	max 1.5 A

Ambient conditions

Ambient temperature	-40 ... 80 °C (-40 ... 176 °F)
---------------------	--------------------------------


Mechanical specifications

Degree of protection	IP67
Material	
Contacts	Gold plated copper alloy
Connector	clear anodized aluminum
Body	CAT5e , teal
Cable	PVC
Slotted nut	Zinc plated steel
Cable	1 m cable length

Compliance with standards and directives

Standard conformity	
Standards	CAT5 (IEC 11801:2002) , CAT5e (TIA 568B:2001) IEC 61076-2-101:2008

Electrical connection



Release date: 2018-11-13 17:07 Date of issue: 2018-11-13 917142_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".