




Dimensions



Model Number


RL24-8-H-80/47/74a

Background suppression sensor with 4-pin, M18 x 1 plastic connector

Features

- Sensing range 80 mm
- Sturdy plastic housing
- Sensitivity adjuster and light-/dark switch
- Pre-fault indication
- 4 programmable time functions

Electrical connection



○ = Light on
● = Dark on

Release date: 2009-08-18 16:38 Date of issue: 2009-08-18 T1560_ENG.xml

Technical data

General specifications

Detection range	20 ... 80 mm
Detection range min.	20 ... 80 mm
Detection range max.	20 ... 90 mm
Light source	LED
Black/White difference (6%/90%)	< 10 %
Approvals	CE
USA	UL
Kanada	CSA
Background suppression	starts from 90 mm
Light type	red, modulated light
Diameter of the light spot	approx. 5 mm at 300 m detection range
Angle of divergence	approx. 1.4 °
Ambient light limit	100000 Lux

Indicators/operating means

Function display	LED yellow, frontal and in the terminal compartment, lit up when light beam is free, flashing when falling short of the stability control
Operating elements	Programming switch for light/dark ON, timer functions
Operating elements	2 potentiometers for timer functions
Operating elements	1 Potentiometer as sensitivity adjuster

Electrical specifications

Operating voltage	U_B	10 ... 30 V DC
Ripple		10 %
No-load supply current	I_0	55 mA

Output

Switching type	Light/dark ON, switchable	
Signal output	2 pnp, antivalent, short-circuit proof, protected against reverse polarity	
Switching voltage	30 V DC	
Switching current	max. 200 mA	
Switching frequency	f	250 Hz
Response time		2 ms
Timer function	GAN, GAB, IAB, GAN-GAB, programmable adjustment range 0.1 ... 10 s	

Standard conformity

Standards	EN 60947-5-2
-----------	--------------


Ambient conditions



Ambient temperature	-20 ... 60 °C (253 ... 333 K)
Storage temperature	-20 ... 75 °C (253 ... 348 K)

Mechanical specifications

Protection degree	IP65
Connection	Flange connector series 714, 4-pin (including unwired, angled cable socket)
Material	
Housing	GF17
Optical face	glass
Mass	100 g

Curves / Diagrams





Release date: 2009-08-18 16:38 Date of issue: 2009-08-18 T1560_ENG.xml