



Tablet computer

Tab-Ex® 04 Pro

TAB-EX04PRODZ2*

- Rugged 10.1 " (25.66 cm) tablet for hazardous areas
- Fast wireless data connection with 5G and Wi-Fi 6
- Latest available Android™ version for this device
- 13 MP rear camera + 8 MP front camera
- Comprehensive security thanks to Samsung KNOX
- Suitable for use with gloves
- Samsung DeX Mode
- Replaceable battery
- MIL-STD-810H
- Memory expansion up to 1 TB possible
- Replaceable SIM
- Non-Camera version possible

Tab-Ex 04 Pro DZ2 (DIV 2 and Zone 2/22), latest available Android firmware release, WWAN (optional), with camera (optional), with microSD card (optional)



Technical Data

Hardware	
Processor	Octa-Core, 4 x 2.4 GHz + 4 x 1.8 GHz Qualcomm Snapdragon SM7325-2-AB
RAM	6 GByte
Camera	
Front camera	8 MP
Main camera	13 MP Autofocus
Video recording resolution	UHD 4K (3840 x 2160 Pixel) @ 30 fps
Internal data memory	128 GByte Free available memory 104.6 GByte
Optional data memory	Micro SD flash card up to 1 TByte
Sensors	Accelerometer, barometer, position sensor, compass, hall sensor, ambient light sensor, proximity sensor
Indicators/operating means	
Display	Can be operated while wearing gloves
Touchscreen technology	Capacitive multitouch
Type	TFT, LCD
Screen diagonal	10.1" (25.66 cm)
Aspect ratio	21.6:18
Resolution	1920 x 1200 (WUXGA)
Brightness	480 cd/m ² (nit)
Colors	16 Mio.
Electrical specifications	
Battery type	Li-Ion battery 28.12 WH 3.8 V 7400 mAh
Operating duration	up to 15 h
Communication	
Mobile standard	
2G	GSM: GSM 850, GSM 900, DCS 1800, PCS 1900
3G	UMTS: B1 (2100), B2 (1900), B4 (AWS), B5 (850), B8 (900)

Release date: 2024-04-05 Date of issue: 2024-04-05 Filename: t217706_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Technical Data

4G	LTE FDD: B1 (2100), B2 (1900), B3 (1800), B4 (AWS), B5 (850), B7 (2.600), B8 (900), B12 (700), B13 (700), B17 (700), B18 (800), B19 (800), B20 (800), B25 (1900), B26 (850), B28 (700), B32 (1500), B66 (AWS-3) LTE TDD: B38 (2600), B40 (2300), B41 (2500) 4 x 4 MIMO: B1 (2100), B3 (1800), B4 (AWS), B7 (2600), B66 (AWS-3), B38 (2600), B41 (2500)
5G	5G Sub6 FDD: n1 (2100), n3 (1800), n5 (850), n7 (2600), n8 (900), n20 (800), n28 (700), n66 (AWS 3) 5G Sub6 TDD: n38 (2600), n40 (2300), n41 (2500), n77 (3700), n78 (3500) 4 x 4 MIMO: n1 (2100), n3 (1800), n7 (2600), n66 (AWS-3), n38 (2600), n41 (2500), n77 (3700), n78 (3500)
WLAN	802.11 a/b/g/n/ac/ax (2,4 GHz + 5 GHz), HE80, MIMO, 1024-QAM
Bluetooth	5.2 with Low Energy support
GPS sensor	GPS, GLONASS, Beidou, Galileo, QZSS
USB	USB 3.2 (Type C)
Connections	Wi-Fi Direct, NFC, ANT+
SIM card	Optional: 1x Nano SIM (4FF)
Software	
Operating system	Android™ 13
Languages	Deutsch , English (default)
Safety	Samsung KNOX 3.x
Ambient conditions	
Ambient temperature	-20 ... 55 °C (-4 ... 131 °F)
Mechanical specifications	
Degree of protection	IP68
Mass	930 g
Dimensions	
W x H x D	170.2 mm x 243.5 mm x 9.9 mm
Data for application in connection with hazardous areas	
ATEX approval	
ATEX certificate	EPS 23 ATEX 1 251 X
ATEX marking	Ⓜ II 3G Ex ic IIC T5 Gc Ⓜ II 3D Ex ic IIIB T80°C Dc
International approvals	
SGS approval	
SGS certificate	Pending
Approved for	Class I, Division 2, Groups A - D T5 Class I, Zone 2, Group IIC T5
IECEX approval	
IECEX certificate	IECEX EPS 23.0079X
IECEX marking	Ex ic IIC T5 Gc Ex ic IIIB T80°C Dc
Approved for	Europe
Further approvals	MIL-STD-810H (Pending)
General information	
Scope of delivery	Tab-Ex 04 Pro incl. battery S Pen Charger Documentation

Accessories

Accessories for this product can be found on the internet at www.pepperl-fuchs.com.