

# Tablet computer

## Tab-IND

### TAB-IND10\* (WIN)



- Rugged, industrial-grade tablet computer
- Mobility and flexibility with multiple accessories
- Enterprise durability and longevity meets sleek design
- Front facing NFC antenna
- Developed in-house
- IP 65 protection class

Tab-IND (industrial grade), 10-inch display, Windows® 10/11, Wi-Fi 6, Intel® N100, 8 GB RAM, 128 GB storage

## Technical Data

Hardware	
Processor	Intel® N100, Quad Core Processor 2.9 GHz
RAM	8 GB LPDDR5
Camera	
Front camera	13MP
Main camera	13MP
Internal data memory	128 GByte UFS
Optional data memory	microSDXC Card Slot, accessible by end user
Sensors	E-compass, accelerometer, gyro, ambient light sensor, proximity sensor Fingerprint sensor (optional)
Indicators/operating means	
Display	Passive stylus support (4 mm tip) Glove support (support of cotton gloves) Improved usage in wet environments (rain & outdoor)
Touchscreen technology	Multi-touch
Screen diagonal	10.1"
Aspect ratio	16:10
Resolution	1920 x 1200 (WUXGA)
Brightness	660 cd/m <sup>2</sup>
Electrical specifications	
Battery type	37.19 Wh 7.7 V 4830 mAh
Operating duration	up to 14 h
Interface	
I/O ports	USB-C, USB 3.1 Gen 1, PD (12V/3A) and DP 1.2 (for fast charging & debugging) Docking connector: USB 3.1 Gen 1, HDMI 1.4b SmartBack Connector for easy USB accessory integration
Communication	
WLAN	IEEE 802.11 ac+r/k/v, Wi-Fi 6, WiDi, WWAN
Bluetooth	Bluetooth® 5.3 Bluetooth® Low Energy
GPS sensor	GPS, GNSS, Galileo (optional)
NFC	Front-facing NFC Secure element
Software	
Operating system	Windows® 10 IoT Enterprise x64
Ambient conditions	
Operating temperature	-20 ... 50 °C (-4 ... 122 °F)

Release date: 2024-04-11 Date of issue: 2024-04-11 Filename: t219109\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com

 PEPPERL+FUCHS

## Technical Data

Storage temperature	-20 ... 60 °C (-4 ... 140 °F)
Relative humidity	10 % ... 90 %
<b>Mechanical specifications</b>	
Degree of protection	IP65
Mass	approx. 817 g
<b>Dimensions</b>	
W x H x D	269.04 mm x 180.66 mm x 12.7 mm
<b>International approvals</b>	
Approved for	EU (UK), US, CA, AU, JP
<b>General information</b>	
Scope of delivery	Tab-IND

## Accessories

Accessories for this product can be found on the internet at [www.pepperl-fuchs.com](http://www.pepperl-fuchs.com).