

# Tablet computer

## Tab-IND

### TAB-IND08\* (WIN)



- Rugged, industrial-grade tablet computer
- Mobility and flexibility with multiple accessories
- Enterprise durability and longevity meets sleek design
- Developed in-house
- IP 65 protection class

Tab-IND (industrial grade), 8-inch display, Windows® 10, LTE (optional), Wi-Fi®, Intel® A3950, 8/4 GB RAM, 128 GB storage

## Technical Data

### Hardware

Processor	Intel® Atom® x7-A3950 (Apollo Lake-I), Quad Core Processor 2.0GHz
RAM	8 GB 4 GB (optional)
Camera	
Front camera	2 MP
Main camera	8 MP
Internal data memory	128 GByte eMMC
Optional data memory	microSDXC Card Slot, accessible by end user
Sensors	E-compass, accelerometer, gyro, ambient light sensor, proximity sensor

### Indicators/operating means

Display	Passive stylus support (4 mm tip) Glove support (support of cotton gloves) Improved usage in wet environments (rain & outdoor)
Touchscreen technology	Multi-touch
Screen diagonal	8.4"
Aspect ratio	16:10
Resolution	2560 x 1600 px (WQXGA)
Brightness	800 cd/m <sup>2</sup>

### Electrical specifications

Battery type	25.08 Wh 7.6 V 3300 mAh
Operating duration	up to 10 h

### Interface

I/O ports	USB-C, USB 3.1 Gen 1, PD (12V/3A) and DP 1.2 (for fast charging & debugging) Docking connector: USB 3.1 Gen 1, HDMI 1.4b SmartBack Connector for easy USB accessory integration
-----------	---

### Communication

Mobile standard	
4G	LTE (optional)
WLAN	IEEE 802.11 ac+r/k/v, WiDi, WWAN (optional)
Bluetooth	Bluetooth® 4.2
GPS sensor	GPS, Glonass, Beidou, Galileo
NFC	Secure element
SIM card	nano SIM Card (LTE version only)

### Software

Release date: 2024-04-11 Date of issue: 2024-04-11 Filename: t219111\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com

 PEPPERL+FUCHS

## Technical Data

Operating system	Windows® 10 IoT Enterprise LTSC x64
<b>Mechanical specifications</b>	
Degree of protection	IP65
Mass	approx. 540 g
Dimensions	
W x H x D	227.83 mm x 150.04 mm x 12.65 mm
<b>General information</b>	
Scope of delivery	Tab-IND

## Accessories

Accessories for this product can be found on the internet at [www.pepperl-fuchs.com](http://www.pepperl-fuchs.com).