

Montageanleitung



Schirmdurchmesser ≤ 5,5 mm

1. Gehäuse auf Kabel auffädeln.
2. Abmanteln, abisolieren, Schirm kürzen, Schirm über Kabelmantel legen und mit einem Kupfer-Tape umwickeln.
3. Litzen anschließen.
4. Gehäuse mit Stecker- bzw. Buchseneinsatz verschrauben und Druckschraube festdrehen.

Schirmdurchmesser > 5,5 mm


1. Gehäuse auf Kabel auffädeln.
2. Abmanteln, abisolieren, Schirm kürzen.
3. Litzen anschließen.
4. Gehäuse mit Stecker- bzw. Buchseneinsatz verschrauben und Druckschraube festdrehen.

Schirm Ø > 5,5 mm



Schirm Ø ≤ 5,5 mm

	Schraubklemmversion	Käfigzugfederversion
A	5	7



Mounting Instruction



Shield-diameter ≤ 5.5 mm

1. Bead housing to cable.
2. Cut off cable coating, strip single cores, shorten shielding braid, put braid over cable coating and wrap it with copper tape.
3. Connect single wires.
4. Screw housing to male or female contact carrier and fix pressing screw.

Shield-diameter > 5.5 mm

1. Bead housing to cable.
2. Cut off cable coating, strip single cores, shorten shielding braid.
3. Connect single wires.
4. Screw housing to male or female contact carrier and fix pressing screw.

shielding braid Ø > 5.5 mm



shielding braid Ø ≤ 5.5 mm

	screw connection	wire clamp connection
A	5	7

