

Bestellbezeichnung / Model Number

VAZ-*T1-FK-G10*-F-*-G

VAZ-T1-FK-G10*-*M*-*F*A



Elektrische Daten / electrical specification

Bemessungsbetriebsspannung U_e ≤ 32 V PELV
Rated operating voltage U_e

Bemessungsbetriebsstrom I_e	VAZ-T1-FK-G10*-F-*M-PUR-V1-G	≤ 1.6 A
Rated operating current I_e	VAZ-2T1-FK-G10*-F-*M-PUR-V1-G	≤ 1.6 A
	VAZ-T1-FK-G10*-*M-PUR-V1-G-F3A	≤ 3 A

Mechanische Daten / Mechanical specification

Anzugsdrehmoment / Tightening torque

Befestigungsschraube / Fastening screw 1,65 Nm / 1.65 Nm

Kabelverschraubung / Cable gland 0,4 Nm / 0.4 Nm

Umgebungsbedingungen / Ambient conditions

Umgebungstemperatur / Ambient temperature -25 ... 70 °C / -13 ... 158 °F

Lagertemperatur / Storage temperature -25 ... 85 °C / -13 ... 185 °F

Zulassungen und Zertifikate / Approvals and certificates

UL-Zulassung / UL approval cULus Listed, Type 1 enclosure

UL File Number E223772
„For use in NFPA 79 Applications only“

UL-anerkannte Flachkabel von P+F / UL recognized flat cable from P+F

Bestell- bezeichnung Order code	Farbe Color	Material	Aderquerschnitt Cross-section	UL cable style	Zulassungen Approvals
VAZ-FK-R-YE*	gelb/ yellow	TPE	2 x 1.5 mm ²	2103	CE  
VAZ-FK-R-BK*	schwarz/ black	TPE	2 x 1.5 mm ²	2103	CE  
VAZ-FK-PUR-YE*	gelb/ yellow	PUR	2 x 1.5 mm ²	20549	CE  
VAZ-FK-PUR-BK*	schwarz/ black	PUR	2 x 1.5 mm ²	20549	CE  
			2 x 2.5 mm ²	21866	

