

8

7

6

5

4

3

2

1

0 10 20 30 40 50 60 70 80 90 100 Vergleichsmaßstab / standard of comparison

F





E

D


C

B

A



Dimension : mm [inch]

product	-		dimensions without tolerances follow	surface description acc.	-	-	-	
-	-		-	-	-	-	-	
				material	colour	p.n.		
				weight/volume: - / -				
CONFIDENTIAL acc. to. ISO 16016			Only valid as long as released in EDM (and together with its 3D CAD model, if applicable)!				scale: 1:2	date: 2016-AUG-23
 Mannheim			Mechanical drawing DO-MIO* -			respons.	-	CAD-2354 -
						approved		
						norm		