





UIC Panel cutout dimensions




6500-01-PM01-PNO-LNO



EPCU mounting












UIC assembly



Note:  
All dimensions are in millimeters

Confidential accoring to ISO 16016	Only valid as long as released in EDM or with a valid production documentation!			scale:	2:5	date:	4-Oct-16
PEPPERL+FUCHS	Mechanical drawing			change notice	respons.	US.DAP	CAD-B0D2A
	6500-01-PM0X-PNO-LNO				approved		
	Twinsburg				norm		sheet 1 of 4

6500-01-PM01-PNO-LNO







Mount Bracket Installation




Note:  
All dimensions are in millimeters

Confidential according to ISO 16016	Only valid as long as released in EDM or with a valid production documentation!			scale:	2:5	date:	4-Oct-16
PEPPERL+FUCHS	Mechanical drawing			change notice	respons.	US.DAP	CAD-B0D2A
	6500-01-PM0X-PNO-LNO				approved		
	Twinsburg				norm		sheet 2 of 4


UIC Panel cutout dimensions











UIC assembly




Note:  
All dimensions are in millimeters

Confidential accoring to ISO 16016		Only valid as long as released in EDM or with a valid production documentation!			scale: 2:5	date: 04-Oct-16
 PEPPERL+FUCHS	Mechanical drawing 6500-01-PM0X-PN0-LN0	change notice		respons.	US.DAP	CAD-B0D2A
				approved		
				norm		
Twinsburg					sheet 3 of 4	

6500-01-PM02-PNO-LNO



Note:  
All dimensions are in millimeters

Confidential according to ISO 16016		Only valid as long as released in EDM or with a valid production documentation!			scale: 2:5	date: 04-Oct-16	
 PEPPERL+FUCHS	Mechanical drawing		change notice	respons. US.DAP	CAD-B0D2A		
	6500-01-PM0X-PNO-LNO			approved			
	Twinsburg				norm	sheet	4 of 4