

Pepperl+Fuchs SE  
Lilienthalstraße 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No. / Nr.: DOC-3299B  
Date / Datum: 2025-07-14

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com

 **PEPPERL+FUCHS**

Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.  
*Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.*

Product family / Produktfamilie

| Product / Produkt    | Description / Beschreibung             |
|----------------------|----------------------------------------|
| V19-a-c-dM-e-V19-f-g | connection cable , M12 connector 8-pin |

The “a”, “c”, “d”, “e”, “f” and “g” marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.  
*Die mit “a”, “c”, “d”, “e”, “f” und “g” markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.*

Directives and Standards / Richtlinien und Normen

| EU-Directive<br>EU-Richtlinie      | Standards<br>Normen  |
|------------------------------------|----------------------|
| 2011/65/EU (RoHS)<br>(L174/88-110) | EN IEC 63000:2018-12 |

| Supplemental Standards<br>Sonstige Normen | Remarks<br>Bemerkungen                                                                                                                                    |
|-------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|
| IEC 61076-2-101:2025                      | Connectors for electronic equipment - Product requirements - Part 2-101: Circular connectors - Detail specification for M12 connectors with screw-locking |

Affixed CE Marking / Angebrachte CE-Kennzeichnung



Signatures / Unterschriften

Mannheim, 2025-07-14

  
ppa. Sebastian Stöber  
Vice President Business Unit  
Systems

  
i.V. Michel Drossmann  
Product Manager

ANNEX TYPE CODE

The “a”, “c”, “d”, “e”, “f” and “g” marked letters of the type code are placeholders and can be replaced by the following code:  
*Die mit “a”, “c”, “d”, “e”, “f” und “g” markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:*

| V19-a-c-dM-e-V19-f-g |                                                                                                                                                                                                                                                                      |
|----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| V19                  | Connector type                                                                                                                                                                                                                                                       |
| a, f                 | G = Straight; W = Angled; GV4A = Straight stainless steel nut; WV4A = Angled stainless steel nut; GU = Straight Ultralock; WU = Angled Ultralock; GT = Straight Teflon; WT = Angled Teflon                                                                           |
| c                    | Blank = Standard; N = Namur, 2-pole; N4 = Namur, 4-pole; GN = Green connector head; GY = Grey connector head; S = Safety, Yellow connector head; 41 = Pin 1 and Pin 4 are crossed; 42 = Pin2 and Pin 4 are crossed; B = Bridged, X = XXL Head                        |
| d                    | Color (blank = Grey; BK = Black; BL = Blue; BN = Brown; GN = Green; YE = Yellow; OR = Orange; RD = Red; VT = Violet; WT = White) + length in m                                                                                                                       |
| e                    | Jacket Material (PUR; PVC; PUR-U; PUR-U/ABG; PUR-U5/ABG; PVC-U; PUR-U/0,75; PUR-ABG; PVC-ABG; PUR-A; PUR-R1; PUR-R2; PUR-R3; PUR-O1; PUR-O2; PUR-O3; POC; PUR-O1S; PUR-O2S; PUR-O3S; TPE; PP; PUR-E1, PUR-E2; PUR-E3; PUR-E1S; PUR-E2S; PUR-E3S, PUR-CAN, PUR-U/CAN) |
| g                    | blank = standard; Y followed by any number = special version                                                                                                                                                                                                         |