

Technical Documentation
01/2026

Gloves Compatibility

Tested Models for VisuNet GXP,
VisuNet FLX and EXTA4
Touchpad (K4 Option)


VisuNet GXP



VisuNet FLX



EXTA4



Rating Scale

Scale	Description
++	High sensitivity, easy to operate
+	Moderate sensitivity, operation possible
-	Low sensitivity, difficult to operate
--	No sensitivity, operation not possible

Nitrile

Manufacturer	Model	VisuNet GXP	VisuNet FLX	EXTA4 (Touchpad, K4 Option)
Nitritec	7840-10	+	++	--
Ansell	AlphaTec Solvex 37-675	++	++	++
Isofield	NS400 Nitril	++	++	++
Kimtech	Pure G3, Nitril Handschuhe 3522	++	++	++
EcoShield	Nitrilhandschuhe PF250 3847	++	++	++
Kimtech	Pure NxT G3 12" Nitril 3523	++	++	++
Schielskin	Xtreme White Nitril 300DI++ 3822	++	++	++
duoSHIELD	PFT Nitrile 240 3845	++	++	++
Honeywell	Flextril 101	++	++	-
Camatril	Antistatik 734	++	++	++
Camatril	Antistatik 731	++	++	+

Gloves Compatibility – Tested Models | 01/2026

Honeywell	Flextril 231	++	++	--
Honeywell	Flextril 211	++	++	-
Nitritec	Nitril 530525 (doppelt)	++	++	-

Latex

Manufacturer	Model	VisuNet GXP	VisuNet FLX	EXTA4 (Touchpad, K4 Option)
UVEX	Unigrip-CL 6627	+	++	--
semperguard	Disposable Latex gloves	++	++	++
Ansell	AccuTech Sterile Coated	++	++	++
Marigold	Emperor ME107	++	++	++
Ansell	Nutex DermaShield (Powder Free)	++	++	++
MAPA	Technic 450	++	++	++
Ansell	AlphaTec 62-201	++	++	+
Kimtech	Pure G3, 12" Latex 3503-01-M	++	++	++
Schieldskin	Xtreme Britgth Latex 300DI+ 3801	++	++	++

Vinyl

Manufacturer	Model	VisuNet GXP	VisuNet FLX	EXTA4 (Touchpad, K4 Option)
Ekastu	628	+	+	--
UVEX	C300 DRY	++	++	++

Leather

Manufacturer	Model	VisuNet GXP	VisuNet FLX	EXTA4 (Touchpad, K4 Option)
ASATEX	Falke-C	++	++	++
ASATEX	88PAWA	-	++	--
Worky	EN 12477-B	++	++	++

Neoprene

Manufacturer	Model	VisuNet GXP	VisuNet FLX	EXTA4 (Touchpad, K4 Option)
NuTex	Dermashield MS 13 11 074	++	++	++
MAPA	Technic 450	++	++	++
Ansell	DermaShield 73-711	++	++	++

Textile

Manufacturer	Model	VisuNet GXP	VisuNet FLX	EXTA4 (Touchpad, K4 Option)
KCL	Thermoplus 955	+	++	--
UVEX	Cotton gloves 89916	++	++	++
Dastex	Baumwollhandschuhe 30080-00	++	++	++

PU

Manufacturer	Model	VisuNet GXP	VisuNet FLX	EXTA4 (Touchpad, K4 Option)
UVEX	Unidur 6641	++	++	++
Dastex	TH 200 30100	++	++	++

Butyl

Manufacturer	Model	VisuNet GXP	VisuNet FLX	EXTA4 (Touchpad, K4 Option)
KCL	Butoject 898	++	++	-

Viton

Manufacturer	Model	VisuNet GXP	VisuNet FLX	EXTA4 (Touchpad, K4 Option)
COMASEC	Solva Plus 0,5 CE0299	+	++	++

Double Gloving

Manufacturer	Model		Manufacturer	Model	VisuNet GXP	VisuNet FLX	EXTA4 (Touchpad, K4 Option)
<i>Inner Gloves</i>			<i>Outer Gloves</i>				
Schioldskin	Xtreme Bright Latex 300DI+ 3801	+	Schioldskin	Xtreme Bright Latex 300DI+ 3801	++	++	-
Kimtech	Pure G3, 12" Latex 3503-01-M	+	Kimtech	Pure G3, 12" Latex 3503-01-M	++	++	++
duoSHIELD	PFT Nitrile 240 3845	+	duoSHIELD	PFT Nitrile 240 3845	++	++	++
Isofield	NS400 Nitril	+	Isofield	NS400 Nitril	++	++	++
Schioldskin	Xtreme Bright Latex 300DI+ 3801	+	duoSHIELD	PFT Nitrile 240 3845	++	++	+
duoSHIELD	PFT Nitrile 240 3845	+	Schioldskin	Xtreme Bright Latex 300DI+ 3801	++	++	+
Schioldskin	Xtreme Bright Latex 300DI+ 3801	+	Isofield	NS400 Nitril	++	++	++
Isofield	NS400 Nitril	+	Schioldskin	Xtreme Bright Latex 300DI+ 3801	++	++	++
Kimtech	Pure G3, 12" Latex 3503-01-M	+	duoSHIELD	PFT Nitrile 240 3845	++	++	++
duoSHIELD	PFT Nitrile 240 3845	+	Kimtech	Pure G3, 12" Latex 3503-01-M	++	++	++
Kimtech	Pure G3, 12" Latex 3503-01-M	+	Isofield	NS400 Nitril	++	++	++
Isofield	NS400 Nitril	+	Kimtech	Pure G3, 12" Latex 3503-01-M	++	++	++
Dastex	Baumwollhandschuhe 30080-00	+	Kimtech	Pure G3, 12" Latex 3503-01-M	++	++	+

Gloves Compatibility – Tested Models | 01/2026

Dastex	Baumwollhandschuhe 30080-00	+	Schioldskin	Xtreme Britght Latex 300DI+ 3801	++	++	++
Dastex	Baumwollhandschuhe 30080-00	+	duoSHIELD	PFT Nitrile 240 3845	++	++	++
Dastex	Baumwollhandschuhe 30080-00	+	Isofield	NS400 Nitril	++	++	++