



Default setting: $Z_w = 1500 \text{ mm}$
 Depth of focus at Z_w : $\text{DoF} = \pm 50 \text{ mm}$

The values ΔX and ΔY apply for read-only tags OIC-C10V2A-CB1 and OIC-C10ST-CB1

Permissible displacement of read-only tag ($\pm\Delta X$ and $\pm\Delta Y$) depending on reading distance Z

Reading window in X and Y direction




Depth of focus (DoF) = ± 50 mm


$Z_w = 1500$ mm

Depth of focus (DoF) = ± 50 mm

$Z_w = 1500$ mm



Reading window in X direction



Reading window in Y direction