


Bulk Spiral Cable

SPK 4x0,25mm² BL900/400/1000




- Resistant to microbes and hydrolysis
- UV resistant
- Halogen-free

Spiral Cable, PUR/PUR, 4-core black



Dimensions



Technical Data

General specifications		
Customization	sheath stripped , with wire end ferrule	
Electrical specifications		
Operating voltage	U _B	max. 250 V AC/DC
Conformity		
Product standard	on the basis of DIN VDE 0812	
Ambient conditions		
Ambient temperature	-25 ... 80 °C (-13 ... 176 °F)	
Pollution degree		3
Mechanical specifications		
Cable		according to IEC/EN 60228 (DIN VDE 0295) class 6
Sheath diameter		5.3 mm
Sheath color		black (similar to RAL 9005)
Number of cores		4
Core cross section		0.25 mm²
Cores color		Core 1: white Core 2: brown Core 3: green Core 4: yellow
Core construction		65 x 0.07 mm Ø
Length	L	2.3 m extension length max. 3.6 m BL: 900 mm A1: 400 mm A2: 44 mm A3: 6 mm B1: 1000 mm B2: 44 mm B3: 6 mm
Cable code		Li F 11Y 11Y 4 x 0,25
Mass		290 g
Material		
Halogen-free		yes
Cable		

Release date: 2024-07-05 Date of issue: 2024-07-05 Filename: 64314772_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**

Technical Data

Sheathing		TMPU
Cores		bare copper (Cu)
Core insulation		TMPU
UV resistance		yes
Oil resistance		yes
Microbial resistance		yes
Hydrolysis resistance		yes

Connection Assignment

_____		_____	WH
_____		_____	BN
_____		_____	GN
_____		_____	YE

Release date: 2024-07-05 Date of issue: 2024-07-05 Filename: 64314772_eng.pdf