



Battery

BAT 3.6 13000 LIT ASSEMBLY

Genuine spare battery for WILSEN devices



Technical Data

Electrical specifications

Nominal voltage	U_N	3.6 V
Nominal capacity		13000 mAh

Ambient conditions

Ambient temperature		-25 ... 70 °C (-13 ... 158 °F)
Storage temperature		permissible: -25 ... 70 °C (-13 ... 158 °F) , with significantly increased self-discharge at temperatures > 30 °C (86 °F) recommended: < 30 °C (86 °F) at < 80% relative humidity

Mechanical specifications

Mass		approx. 100 g
Dimensions		
Height		65 mm
Diameter		38 mm

Additional Information



YouTube Video: Battery Replacement
https://www.youtube.com/watch?v=CG1_72SXxkM



Video for Battery Replacement

You can find a video describing the battery replacement on YouTube via the following link:
https://www.youtube.com/watch?v=CG1_72SXxkM
Alternatively, you can also scan the QR code provided here to watch the video.