


Accessory DGE ShieldScan Transfer Loop



Flexible connection cable to the door controller, standard 2.5 m, including corrugated hose and holder

Dimensions



Technical Data

Ambient conditions		
Ambient temperature		-30 ... 80 °C (-22 ... 176 °F)
Mechanical specifications		
Length	L	total length 2500 mm corrugated hose 660 mm
Diameter		External diameter: approx. 11.2 mm corrugated hose
Connection		plug 10-pin
Material		corrugated hose : PC (Polycarbonate) Wall bracket : PA6
Cable		
Sheath diameter		5.4 mm
Bending radius		> 10 x cable diameter, movable installation
Mass		approx. 114 g , total approx. 92 g , Connection cable approx. 5 g , Wall bracket
General information		
Scope of delivery		Connection cable , corrugated hose , Wall bracket
Suitable series		
Series		ShieldScan

Release date: 2026-02-27 Date of issue: 2026-02-27 Filename: 70120467_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS


Connection

NPN/PNP			Solid-state relay		
1	BN	0V	1	BN	0V
2	GN	24V	2	GN	24V
3		n.c.	3	PK	COMMON BGS
4	GY	BGS OUT	4	GY	BGS OUT
5		n.c.	5		n.c.
6		n.c.	6	YE	COMMON BS
7	WH	BS OUT	7	WH	BS OUT
8		n.c.	8		n.c.
9	RD	Test +	9	RD	Test +
10	BU	Test -	10	BU	Test -

Connection Assignment



Mounting



Release date: 2026-02-27 Date of issue: 2026-02-27 Filename: 70120467_eng.pdf