


Dimensions



Technical Data

Ambient conditions		
Ambient temperature		-30 ... 60 °C (-22 ... 140 °F)
Mechanical specifications		
Material		Polycarbonate (PC)
Mass		77.1 g
Dimensions		
Height		16.9 mm
Width		61 mm
Length		255 mm
General information		
Scope of delivery		2x spacer wedge 6x screws
Suitable series		
Series		ShieldScan