


LED indicator assembly

CFS.MOD.LCS.PI024V.K01.SP




- Component for appropriately certified Ex d enclosures
- Ex db and Ex tb certified
- Polyamide and brass nickel-plated



Connection Assignment



Dimensions



Dimension values see mechanical specifications.
Image and drawing are generic for this device type and may deviate from the specific variant.

Technical Data

Electrical specifications

Operating voltage	24 V max. AC/DC
Operating current	11 mA max.
Terminal capacity	1.5 mm ²
Terminal torque	1.2 Nm
Function	Pilot light with module
Lens color	See accessories section
Labeling	none

Mechanical specifications

Thread size (TD)	M28
Degree of protection	IP66
Material	

Release date: 2026-04-10 Date of issue: 2026-04-10 Filename: 70182758_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Technical Data

Housing	Polyamide (PA) , brass nickel-plated
Finish	inherent color black
Mass	58 g
Dimensions	
Actuator head diameter (D2)	33.5 mm
Panel wall thickness (PT)	15 ... 30 mm
Length outside enclosure (H)	33 mm
Total length (L)	109.5 mm
Tightening torque	Actuator head : 2 Nm
Mounting	use with lid-mounted contact modules
Ambient conditions	
Service temperature	-40 ... 70 °C (-40 ... 158 °F)
Data for application in connection with hazardous areas	
EU-type examination certificate	CML 17 ATEX 1341U
Marking	Ⓔ II 2 GD Ex db IIC Gb Ex tb IIIC Db
International approvals	
IECEx approval	IECEx CML 17.0181U
UKCA approval	CML 21 UKEX 1422U
Conformity	
Degree of protection	EN 60529
General information	
Supplementary information	EC-Type Examination Certificate, Statement of Conformity, Declaration of Conformity, Attestation of Conformity and instructions have to be observed where applicable. For information see www.pepperl-fuchs.com .
Enclosure type	EJB , EJBX , GUB , GUBX
Accessories	
Optional accessories	CFS.LR.K50.SP CFS.LG.K50.SP CFS.LO.K50.SP CFS.LW.K50.SP