




Converter Connection Cable VOI-F331-24V-DB9

Converter connection cable, 24 V to 5 V, with a connectors for trigger, RS-232, I/Os, and a socket for voltage supply connection



Dimensions




Technical Data

General specifications	
Connector 1	
Connection	socket
Construction type	M12
Style	straight
Locking	screw connection
Number of pins	8

Technical Data

Coding	A-coded	
Degree of protection		IP65
Connector 2		
Connection		plug
Construction type		M12
Style		straight
Locking		screw connection
Number of pins		4
Coding	A-coded	
Degree of protection		IP65
Connector 3		
Connection		socket
Construction type		M8
Style		straight
Locking		screw connection
Number of pins		4
Coding	A-coded	
Degree of protection		IP65
Connector 4		
Connection		socket
Construction type		Sub-D
Style		straight
Locking		screw connection
Number of pins		9
Degree of protection		IP20
Electrical specifications		
Operating voltage	U _B	10 ... 30 V DC ± 10 %
Ambient conditions		
Ambient temperature		-20 ... 60 °C (-4 ... 140 °F)
Storage temperature		-40 ... 70 °C (-40 ... 158 °F)
Mechanical specifications		
Note		Trigger connection for 24 V

Connection Assignment



Release date: 2026-03-27 Date of issue: 2026-03-27 Filename: 70195358_eng.pdf