


Converter Connection Cable VOI-F331-24V



Converter connection cable, 24 V to 5 V, with an open cable end for connecting trigger, RS-232, I/Os, and a socket for voltage supply



Dimensions



Technical Data

General specifications

Connector 1		
Connection		socket
Construction type		M12
Style		straight
Locking		screw connection
Number of pins		8
Coding		A-coded
Degree of protection		IP65
Connector 2		
Connection		cable end

Electrical specifications

Operating voltage	U _B	10 ... 30 V DC ± 10 %
-------------------	----------------	-----------------------

Release date: 2026-03-27 Date of issue: 2026-03-27 Filename: 70195360_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Technical Data

Ambient conditions		
Ambient temperature		-20 ... 60 °C (-4 ... 140 °F)
Storage temperature		-40 ... 70 °C (-40 ... 158 °F)
Mechanical specifications		
Plug connector		
Shielding		shield connected to screw connection
Degree of protection		IP65
Cable		
Sheath color		black (similar to RAL 9005)
Number of cores		8
Material		
Plug connector		
Screw connection		Zinc diecast, nickel-plated
Body		PVC, black
Cable		
Sheathing		PVC

Connection Assignment

