

Model Number

V1-SLEEVE-100M-SI

Silicone rubber, one piece

Features

- Chemical, moisture, and heat resistant
- Provides cable connector end with weld slag protection
- Expandable to cover irregular shapes

Dimensions

Technical data

General specifications

Inside diameter	12.7 mm
-----------------	---------

Ambient conditions

Ambient temperature	-75 ... 220 °C (-103 ... 428 °F)
---------------------	----------------------------------

Mechanical specifications

Material	silicone coated fiberglass	
Cable		
Color	white	
Length	L	100 m

Electrical connection