

**Combining technologies.
Preventing collisions.
Maximizing performance.**

Dual-Technology Sensor for
Automatic Sliding Doors

MotionScan




Your automation, our passion.

 **PEPPERL+FUCHS**

Open Quickly, Close Safely—MotionScan for Better Performance

The two-in-one MotionScan sensor from Pepperl+Fuchs manages the smooth flow of large numbers of people going through doors, while safely identifying and protecting individuals from accidents. The large radar detection field senses when people approach and opens doors in a timely manner, while the large infrared protection field prevents collisions.



Early Detection for Quick Door Opening

The high-performance MotionScan radar module emits a pulse that instructs automatic sliding doors to open. The radar detection field of up to 4 × 4 m quickly and reliably senses approaching people, ensuring unrestricted movement even for large groups.

Increased Safety when Closing Doors

To avoid the danger presented by closing doors, the active infrared sensor built into MotionScan ensures that the leading edge of the door is protected. To provide the highest degree of safety and collision protection, three rows of adjustable infrared emitters are used to create a protection field starting from the door up to a maximum distance of 1.10 m.



For more information, visit
[pepperl-fuchs.com/motionscan](https://www.pepperl-fuchs.com/motionscan)

Excerpt of technical data

MotionScan

Mounting height	2 m ... 3.20 m
Operating voltage	12 ... 24 V AC/DC ± 10 %
Functional safety	SIL 2, PL d
Temperature range	-20 °C ... +60 °C
Degree of protection	IP54
Standards	RED 2014/53/EU EN 16005:2012 DIN 18650-1:2010 EN 12978:2003 +A1:2009 EN ISO 13849-1:2015 AutSchR 12/1997

Reliability in Any Situation


Whether high-gloss marble, stone tiles, or grids—MotionScan works well with various kinds of floor surfaces. The adjustable protection and detection fields, the integrated direction monitoring, as well as the mounting height of up to 3.20 m make MotionScan ideal for a wide range of applications.

Easy to Install and Operate


With its automatic teach-in function and the installation instructions printed on the sensor, installing and commissioning MotionScan is quick and easy. The operating mode is user-friendly and clearly displayed via a multicolored LED.

Highlights

- Large 4 × 4 m radar detection field and fast response time open doors quickly for a smooth flow of pedestrian traffic
- The highest degree of safety due to the large adjustable infrared protection field
- Reliable operation on various floor surfaces
- Easy to install and user-friendly with automatic teach-in function and a multicolored LED



Infrared protection field in front of the door (EN 16005)



Infrared protection field on both sides of the door



Adjustable Protection and Detection Fields

Your automation, our passion.

- Industrial Sensors
- Industrial Communication and Interfaces
- Enterprise Mobility
- Hazardous Area Products and Solutions

www.pepperl-fuchs.com

Subject to modifications • © Pepperl+Fuchs
Printed in Germany • Part. No. 70186975 10/24 • public



Pepperl+Fuchs Quality

Download our latest policy here:

www.pepperl-fuchs.com/quality